


RoHS


REV.	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框	Tong.Deng	Roy.Qing	2023.09.03





P.C.B Hole Layout





No.of PIN/ROW	Dimension A	Dimension B			
2*02	2. 54	5. 08	2*21	50. 80	53. 34
2*03	5. 08	7. 62	2*22	53. 34	55. 88
2*04	7. 62	10. 16	2*23	55. 88	58. 42
2*05	10. 16	12. 70	2*24	58. 42	60. 96
2*06	12. 70	15. 24	2*25	60. 96	63. 50
2*07	15. 24	17. 78	2*26	63. 50	66. 04
2*08	17. 78	20. 32	2*27	66. 04	68. 58
2*09	20. 32	22. 86	2*28	68. 58	71. 12
2*10	22. 86	25. 40	2*29	71. 12	73. 66
2*11	25. 40	27. 94	2*30	73. 66	76. 20
2*12	27. 94	30. 48	2*31	76. 20	78. 74
2*13	30. 48	33. 02	2*32	78. 74	81. 28
2*14	33. 02	35. 56	2*33	81. 28	83. 82
2*15	35. 56	38. 10	2*34	83. 82	86. 36
2*16	38. 10	40. 64	2*35	86. 36	88. 90
2*17	40. 64	43. 18	2*36	88. 90	91. 44
2*18	43. 18	45. 72	2*37	91. 44	93. 98
2*19	45. 72	48. 26	2*38	93. 98	96. 52
2*20	48. 26	50. 80	2*39	96. 52	99. 06
			2*40	99. 06	101. 60

SPecifications
Current Rating: 3Ampere
Insulation Resistance: 1000MΩ MIN.
Dielectric Withstading: 600V AC
Contact Resistace: 20mΩ Max.
Operating Temprature: -40℃ to +105℃
Material
Post: Brass Tin/Plated
Gold/Tin Over Nickel
Bass: PA6T/ UL 94V-0

X.±0.50	X.°±
.X±0.25	.X°±
.XX± 0.15	.XX°±
.XXX± 0.10	.XXX°±
UNITS:	mm

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN

PART NO: PZ254V-22-30-H20-L150

TITLE: 2.54mm Pin Header Connectors

APPD: Roy.Qing 2024.04.23

CHKD: Cheng.Ke 2024.04.23

DRAW: Tong.Deng 2024.04.23

XFCN兴飞连接器
0769-82001899
www.xfconn.com

DWG NO:

SCALE	SHEET	REV.
NONE	4/1	A1