50A Three-Phase Bridge Rectifier

1 General Description

1.1 Features

- Glass passivated chip
- Ideal for printed circuit boards
- High surge current capability
- High temperature soldering guaranteed:265℃/10 seconds


REVERSE VOLTAGE
800-1600V
OUTPUT CURRENT
50Ampere

1.2 Typical Applications

- Inverter for AC or DC motor control
- Current stabilized power supply
- Input rectifiers for variable frequency drives
- Input rectifiers for PWM inverter

1.3 Mechanical Data

- Case: Reliable low cost construction utilizing molded plastic technique
- Terminals: Plated leads solderable per MIL-STD-750, Method 2026
- Mounting Position: Any
- Polarity: Marked on body



2 Maximum Ratings(TA=25℃ Unless otherwise specified)

PARAMETER	SYMBOL	CONDITIONS	SGBJ5008	SGBJ5010	SGBJ5012	SGBJ5016	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	-	800	1000	1200	1600	V
Non-repetitive Peak Reverse Voltage	V_{RSM}	-	900	1100	1300	1700	V
Output Current	I_D	Three Phase, Full Wave Tc =95℃	50				A
Surge Forward Current	I_{FSM}	Tj=25℃, t = 50Hz(10ms), V_R = 0V	500				A
Circuit Fusing Consideration	I^2t	t = 10ms ,Tj =25℃	1250				A^2s
Isolation Breakdown Voltage	V_{ISO}	AC50Hz/60Hz;R.M.S; 1min	2500				V
Operating Junction Temperature	T_J	-	-40 to +150				℃
Storage Temperature	T_{STG}	-	-40 to +125				℃
Mounting Torque	M_S	(Recommended torque:0.65 N·m)	0.8				N·m
Thermal Impedance, Max	$R_{\theta J-C}$	Junction to Case(Per Total)	0.5				℃/W
		Junction to Case(Per Diode)	3				

3 Electrical Characteristics(TA=25℃ Unless otherwise specified)

PARAMETER	SYMBOL	CONDITION	SGBJ5008	SGBJ5010	SGBJ5012	SGBJ5016	UNIT
Forward Voltage Drop, Max	V_{FM}	Tj = 25℃ I_F = 25A	1.18 Max.				V
Repetitive Peak Reverse Current, Max	I_{RRM}	Tj =25℃ V_R = V_{RRM}	5 Max.				μA
		Tj =150℃ V_R = V_{RRM}	3 Max.				mA
Threshold Voltage, for power loss calculation only	V_{T0}	Tj =125℃	0.75				V
Slope Resistance, for power loss calculation only	r_T	Tj =125℃	7				mΩ

4 Characteristics Curves(TA=25℃ Unless otherwise specified)




Fig1. Power Dissipation




Fig2. Forward Current Derating Curve




Fig3. Forward Characteristics




Fig4. Transient Thermal impedance





Fig5. Max Non-Repetitive Forward Surge Current

5 Package Outline Dimensions



Symbol	UNIT(mm)	
	Min	Max
A	3.80	4.20
B	0.40	0.60
C	5.20	5.60
D	2.80	3.70
E	13.90	14.50
F	3.50	3.90
G	0.65	0.75
H	34.70	35.30
I	17.30	17.70
J	3.90	4.50
K	24.70	25.30
L	19.50	20.20
M	1.30	1.70
N	2.10	2.30
O	0.90	1.10
P	14.70	15.30
Q	29.70	30.30

6 Ordering Information

PACKAGE	UNIT WEIGHT (g)	BOX (pcs)	CARTON (pcs)
SGBJ	Approximate 12.7	100	1000

Disclaimer

1. All information contained in this document is for reference only. Shandong Baocheng Electronics Co.,Ltd reserves the right to revise this document, product specifications and related data at any time without prior notice. Customers shall obtain and confirm the latest product documents and specifications before purchasing or using the products.

2. Under no circumstances shall the Company be liable for any failure or damage caused by the operation of semiconductor devices beyond the maximum rated values.

3. Shandong Baocheng Electronics Co.,Ltd does not warrant the suitability of its products for any specific application and assumes no responsibility for customer's complete machine design or application debugging. Without written approval, products are prohibited from being used as key components of life support equipment. The Company shall not be liable for any consequences arising from unauthorized use.

4. No intellectual property license of Shandong Baocheng Electronics Co.,Ltd is granted, explicitly or implicitly, through this document.