
UMW ES2A THRU ES2J

Surface Mount Superfast Recovery Rectifier


1.Features


- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Superfast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

2.Pinning Information



3.Reverse Recovery Time Characteristic And Test Circuit Diagram





Set time Base for 10ns/div

Note:

1.Rise Time = 7ns, max.
Input Impedance = 1megohm,22pF.

2.RiER Time =10ns, max.
Source Impedance = 50 ohms.

4.Absolute Maximum Ratings and Characteristics

Ratings at 25°C ambient temperature unlss otherwise specified.

Single phase half-wave 60Hz,resistive or inductive load,for capacitive load current derate by 20%.

Parameter		Symbols	ES2A	ES2B	ES2C	ES2D	ES2E	ES2G	ES2J	Units
Maximum repetitive peak reverse voltage		V_{RRM}	50	100	150	200	300	400	600	V
Maximum RMS voltage		V_{RMS}	35	70	105	140	210	280	420	V
Maximum DC blocking voltage		V_{DC}	50	100	150	200	300	400	600	V
Maximum average forward rectified current at T_C=125°C		$I_{F(AV)}$	2							A
Peak forward surge current 8.3ms single half sine wave superimposed on rated load		I_{FSM}	50							A
Maximum forward voltage at 2A		V_F	1				1.25		1.68	V
Maximum DC reverse current at	T_A=25°C	I_R	5							μA
at rated DC blocking voltage	T_A=125°C		100							μA
Typical junction capacitance at V_R=4V, f=1MHz		C_J	40							pF
Maximum Reverse Recovery Time (1)		t_{rr}	35							ns
Typical Thermal Reristance (2)		$R_{\theta JA}$	60							°C/W
Operating junction and storage temperature range		T_J,T_{STG}	-55 to 150							°C

Note:

1.Measured with I_F=0.5A, I_R=1A, I_{rr}=0.25A.

2.P.C.B. mounted with 1.0 X 1.0" (2.54 X 2.54 cm) copper pad areas.

5.Typical Characteristic




Figure 1: Maximum Average Forward Current Rating




Figure 2: Typical Reverse Characteristics




Figure 3: Typical Forward Characteristics




Figure 4: Typical Junction Capacitance





Figure 5: Maximum Non-Repetitive Peak Forward Surage Current


6.SMA Package Outline Dimensions



DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	B1	B2	b	D	E	E1	θ
Min	4.9	4.05	0.97	2.18	2.15	1.0	2.55	1.38	1.8	2.0	5°
Max	5.1	4.15	1.03	2.38	2.25	1.4	2.65	1.42	2.0	2.2	

7.Ordering Information



Order Code	Marking	Package	Base QTY	Delivery Mode
UMW ES2A	ES2A	SMA	2000	Tape and reel
UMW ES2B	ES2B	SMA	2000	Tape and reel
UMW ES2D	ES2D	SMA	2000	Tape and reel
UMW ES2G	ES2G	SMA	2000	Tape and reel
UMW ES2J	ES2J	SMA	2000	Tape and reel

8.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.