CESD3V3D5

1-Line Uni-directional TVS Diode

Features

- Ultra small package: SOD-523
- Protects one data or power line
- Ultra low leakage: nA level
- Operating voltage: 3.3V
- Low clamping voltage
- 2-Pin leadless package
- Complies with following standards:
  – IEC 61000-4-2 (ESD) immunity test
    Air discharge: ±30kV
    Contact discharge: ±30kV
  – IEC61000-4-5 (Lightning) 11A (8/20μs)
- RoHS Compliant




SOD-523

Mechanical Characteristics

- Package: SOD-523
- Case Material: “Green” Molding Compound.
- Terminal Connections: See Diagram Below
- Marking Information: See Below

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- Digital Cameras
- Peripherals
- Audio Players
- Keypads, Side Keys, LCD Displays



Circuit diagram

Ordering Information

Part Number	Packaging	Reel Size	Marking
CESD3V3D5	3000/Tape & Reel	7 inch	ZE


Absolute Maximum Ratings (T_A=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	130	W
Peak Pulse Current (8/20μs)	Ipp	11	A
ESD per IEC 61000−4−2 (Air) ESD per IEC 61000−4−2 (Contact)	V_{ESD}	±30 ±30	kV
Operating Temperature Range	T_J	−55 to +125	°C
Storage Temperature Range	Tstg	−55 to +150	°C


Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	V_{RWM}			3.3	V	Pin 1 to Pin 2
Breakdown Voltage	V_{BR}	4.0			V	I_T = 1mA, Pin 1 to Pin 2
Reverse Leakage Current	I_R			1.0	μA	V_{RWM} = 3.3V, Pin 1 to Pin 2
Forward Voltage	V_F			1.2	V	I_F = 10mA, Pin 2 to Pin 1
Clamping Voltage	V_C			8	V	I_{PP} = 1A (8 x 20μs pulse), Pin 1 to Pin 2
Clamping Voltage	V_C		10	13	V	IPP = 11A (8 x 20μs pulse)
Junction Capacitance	C_J		60		pF	VR = 0V, f = 1MHz


Typical Performance Characteristics (T_A=25°C unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time




Clamping Voltage vs. Peak Pulse Current (tp = 8/20μs)



TLP Measurement




8 X 20μs Pulse Waveform



ESD Clamping Voltage


8 kV Contact per IEC61000−4−2

SOD-523 Package Outline Drawing



SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.51	- -	0.77	0.020	- -	0.031
A1	0.50	- -	0.70	0.020	- -	0.028
b	0.25	- -	0.35	0.010	- -	0.014
c	0.08	- -	0.15	0.003	- -	0.006
D	0.75	- -	0.85	0.030	- -	0.033
E	1.10	- -	1.30	0.043	- -	0.051
E1	1.50	- -	1.70	0.059		0.067
E2	0.20REF			0.008REF		
L	0.01	- -	0.07	0.001	- -	0.003
Θ	7° REF			7° REF		

Suggested Land Pattern



Unit：mm