

TVS Diodes Axial Leaded

1 General Description

1.1 Description

- The AK3 series of high power TVS diode is specially designed for meeting severe surge test environment of both AC and DC line protection applications. It features a very fast response and ultra low clamping characteristics over traditional metal oxide (MOV) solutions.They can be connected in series and / or parallel to create a very high surge current protection solution..





1.2 Features

- Very low clamping voltage
- Ultra compact: less than one-tenth the size of traditional discrete solutions
- Sharp breakdown voltage
- Low slope resistance
- Bi-directional
- Foldbak technology for superior clamping factor
- Symmetric in leads width for easier soldering during assembly.
- IEC-61000-4-2 ESD 15kV(Air), 8kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4
- Halogen-free
- RoHS compliant
- Glass passivated junction
- Pb-free E4 means 2nd level interconnect is Pb-free and the terminal finish material is Silver

Flow/Wave Soldering(Solder Dipping)	
Peak Temperature:	265℃
Dipping Time:	10 seconds
Soldering:	1 time

1.3 Mechanical Data

- Case: Epoxy encapsulated
- Terminals: Silver plated leads,solderable per MIL-STD-750 Method2026
- Weight:Contact manufacturer

2 Maximum Ratings(TA=25℃ Unless otherwise specified)

PARAMETER	SYMBOL	VALUE	UNIT
Current Rating 1	I_{PP}	10	KA
Operating Junction Temperature Range	T_J	-55 to +125	℃
Storage Temperature Range	T_{STG}	-55 to +125	℃

Note:1.Rated I_{PP} with 8/20μs pulse.

3 Electrical Characteristics(TA=25℃ Unless otherwise specified)

Part Number	Reverse Stand-off Voltage	Breakdown Voltage @IT		Test Current	Maximum Clamping Voltage@IPP(V)	Maximum Peak Pulse Current	Maximum Reverse Leakage@VRWM
	VRWM(V)	VBR MIN (V)	VBR MAX (V)	IT (mA)	VC(V)	8/20μs (KA)	IR (μA)
AK10-015C-BC	15	16	19	10	28	10	1
AK10-030C-BC	30	32	37	10	58	10	1
AK10-038C-BC	38	40.5	49.5	10	63.5	10	1
AK10-058C-BC	58	64	70	10	110	10	1
AK10-066C-BC	66	72	80	10	120	10	1
AK10-076C-BC	76	85	95	10	140	10	1
AK10-170C-BC	170	180	220	10	260	10	1
AK10-190C-BC	190	200	245	10	290	10	1
AK10-240C-BC	240	250	285	10	340	10	1
AK10-300C-BC	300	310	345	10	480	10	1
AK10-380C-BC	380	401	443	10	520	10	1
AK10-430C-BC	430	440	490	10	625	10	1
AK10-530C-BC	530	560	619	10	750	10	1

4 Characteristics Curves(TA=25℃ Unless otherwise specified)

Figure 1 - Non Lead-free Profile




Figure 2 - Lead-free Profile




Figure 3 - Peak Power Derating




Figure 4 - Typical Peak Pulse Power Rating Curve




Figure 5 - Typical V_{BR} Vs Junction Temperature






Figure 6 -Surge Response (8/20 Surge current waveform)




Note:

The power dissipation causes a change in avalanche voltage during the surge and the avalanche voltage eventually returns to the original value when the transient has passed.

Figure 7 - Pulse Waveform



5 Package Outline Dimensions



Symbol		Dimensions Millimeters
A		24.15±1.00
A-530C		29.5±1.00
B		2.40±0.60
C		6.00 min
D		16.0 max
E		1.28±0.02
F		16.0 max
G	30C/38C	6.0 max
	58C/66C/76C/86C	8.0 max
	170C/190C/240C	14.0 max
	300C/380C/430C	18.0 max
	530C	22.0 max
L1=L2 tolerance ±1.20mm		

6 Ordering Information

PACKAGE	UNIT WEIGHT (g)	BOX (pcs)	CARTON (pcs)
BPSS	consult	56	not fixed

Disclaimer

1. All information contained in this document is for reference only. Shandong Baocheng Electronics Co.,Ltd reserves the right to revise this document, product specifications and related data at any time without prior notice. Customers shall obtain and confirm the latest product documents and specifications before purchasing or using the products.

2. Under no circumstances shall the Company be liable for any failure or damage caused by the operation of semiconductor devices beyond the maximum rated values.

3. Shandong Baocheng Electronics Co.,Ltd does not warrant the suitability of its products for any specific application and assumes no responsibility for customer's complete machine design or application debugging. Without written approval, products are prohibited from being used as key components of life support equipment. The Company shall not be liable for any consequences arising from unauthorized use.

4. No intellectual property license of Shandong Baocheng Electronics Co.,Ltd is granted, explicitly or implicitly, through this document.