



1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output DC-DC Converter

5Vin DC-DC Converter 1 Watt

- ⊕ Continuous short-circuit protection
- ⊕ No-load input current as low as 5mA
- ⊕ Operating temperature range: -40°C to +105°C
- ⊕ High efficiency up to 85%
- ⊕ Isolation voltage: 1.5kVDC/min, 3kVDC/1s
- ⊕ International standard pin-out
- ⊕ Compact SIP package
- ⊕ UL62368, EN62368 approval

The 1S4AE_1.5UP series are specially designed for applications where an isolated voltage is required in a distributed power supply system. They are suitable for: pure digital circuits, low frequency analog circuits, relay-driven circuits and data switching circuits.



UL-62368-1 (E347551)

Common specifications			
Short Circuit Protection	Continuous, self-recovery		
Operating Temperature	-40 ~ 105°C Derating if the temperature ≥85°C, (see Fig. 2)		
Storage Temperature	-55 ~ 125°C		
Casing Temperature Rise	Ta=25°C		°C
	• 3.3VDC output	25	°C
	• Other output	15	°C
Pin Welding Resistance Temperature	Welding spot is 1.5mm away from the casing, 10 seconds	300°C	
Storage Humidity	Non-condensing	95 %RH	
Switching Frequency	100% load, nominal input voltage	270	KHz
MTBF	3500,000h (MIL-HDBK-217F@25)		
Casing Material	Black flame-retardant and heat-resistant plastic (UL94 V-0)		
Package Dimensions	11.60x6.00x10.16mm		
Weight	1.3g(Typ.)		
Cooling methods	Free air convection		

Output specifications					
Item	Test condition	Min	Typ	Max	Units
Output voltage accuracy	See tolerance envelope curve(Fig. 1)				
Line regulation	Input voltage change: ±1%			1.5	%
	• 3.3VDC output			1.2	%
	• Others				
Load regulation	10% to 100% load		15	20	%
	• 3.3VDC output		10	15	%
	• 5VDC output		8	10	%
	• 9VDC output		7	10	%
	• 12VDC output		6	10	%
	• 15VDC output		5	10	%
	• 24VDC output				
Ripple & Noise*	20MHz Bandwidth		30	75	mVp-p
	• Other output		50	100	mVp-p
	• 24VDC output				
Temperature Drift Coefficient	100% load		±0.02		%/°C

Note: *Ripple and noise tested with "parallel cable" method, please see DC-DC Converter Application Notes for specific operation methods.

Isolation specifications					
Item	Test condition	Min	Typ	Max	Units
Isolation voltage	Input-output, leak current lower than 1mA				
	• 1 minute test time	1500			VDC
	• 1 second test time	3000			VDC
Isolation resistance	IO, test at 500VDC	1000			MΩ
Isolation capacitance	IO , 100KHz/0.1V		20		pF

Input specifications					
Item	Test condition	Min	Typ	Max	Units
Input current (full load / no-load)	• 3.3/5VDC output	270/5	286/10		mA
	• 9/12VDC output	241/12	254/20		mA
	• 15/24VDC output	241/18	254/30		mA
Reflected ripple current*			15		mA
Surge Voltage (1sec. max.)		-0.7	9		VDC
Input filter	Capacitor filter				
Hot plug	Unavailable				

* Reflected ripple current testing method please see DC-DC Converter Application Notes for specific operation.

EMC specifications					
Emissions	CE	CISPR32/EN55032	CLASS B (EMC recommended circuit)		
Emissions	RE	CISPR32/EN55032	CLASS B (EMC recommended circuit)		
Immunity	ESD	IEC/EN61000-4-2	Air ±8kV, Contact ±4kV perf. Criteria B		

Example:

1S4AE_0505S1.5UP

1 = 1Watt; S4 = SIP4; A = Pinning; E = Cost effective; 05 = 5Vin; 05 = 5Vout; S = Single Output; 1.5 = 1.5kVDC; U = Unregulated output; P = Short circuit protection

Note:

- If the product is not operated within the required load range, the product performance cannot be guaranteed to comply with all parameters in the datasheet;
- The maximum capacitive load offered were tested at input voltage range and full load;
- Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta = 25°C, humidity <75%RH with nominal input voltage and rated output load;
- All index testing methods in this datasheet are based on our Company's corporate standards;
- We can provide product customization service, please contact our technicians directly for specific information;
- Products are related to laws and regulations: see "Features" and "EMC";
- Classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.




1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Product Selection Guide

Part Number	Certification	Input Voltage [VDC]		Output Voltage [VDC]	Output Current [mA, Max./Min]	Efficiency ⁽²⁾ [%, Min./Typ.] @ Full Load	Capacitive load [μ F, Max]
		Nominal	Range				
1S4AE_0503S1.5UP	UL	5	4.5-5.5	3.3	303/30	70/74	2400
1S4AE_0505S1.5UP	UL	5	4.5-5.5	5	200/20	78/82	2400
1S4AE_0512S1.5UP	UL	5	4.5-5.5	9	111/12	79/83	1000
1S4AE_0512S1.5UP	UL	5	4.5-5.5	12	84/9	79/83	560
1S4AE_0515S1.5UP	UL	5	4.5-5.5	15	67/7	79/83	560
1S4AE_0524S1.5UP	UL	5	4.5-5.5	24	42/4	81/85	220





Typical Characteristic Curves



1S4AE_1.5UP series


1W, Fixed input voltage, isolated & unregulated single output DC-DC Converter

Efficiency curves



Typical application


If it is required to further reduce input and output ripple, a filter capacitor can be connected to the input and output terminals, see Fig.3. Moreover, choosing suitable filter capacitor is very important, start-up problems may be caused by too large capacitance. To ensure the modules running well, the recommended capacitive load values as shown in Table 1.



Recommended capacitive load value table (Table 1)

Vin (VDC)	Cin(μF)	Vout (VDC)	Cout (μF)
5	4.7	3.3/5	10
		9/12	2.2
		15/24	1

EMC solution-recommended circuit



EMC recommended circuit value table (Table 2)

Input voltage 5VDC	Output voltage (VDC)		
	3.3/5/9	12/15/24	
EMI	C1/C2	4.7μF /25V	4.7μF /25V
	CY		1nF/4KVDC VISHAY HGZ102MBP TDK CD45-E2GA102M-GK
	C3	Refer to the Cout in table 1	
	LDM	6.8μH	6.8μH


Note:

In the case of actual use, the requirements for EMI are high, it is subject to CY.

1S4AE_1.5UP series

1W, Fixed input voltage, isolated & unregulated single output
DC-DC Converter

Mechanical dimensions and recommended layout




Note:

Unit :mm[inch]

Pin section tolerances :±0.10[±0.004]

General tolerances:±0.25[±0.010]

THIRD ANGLE PROJECTION



Note : Grid 2.54*2.54mm

Pin-Out	
Pin	Function
1	GND
2	Vin
3	0V
4	+Vo