SIEMENS

Data sheet 3RQ3118-2AM01



Output coupler with plug-in Relay, 1 CO, hard gold-plated Spring-type terminal (push-in) 24 V DC Enclosure width 6.2 mm Thermal current 6A

product brand name	SIRIUS
product category	SIRIUS 3RQ3 coupling relays in slim design
product designation	Coupling relays with plug-in relay
design of the product	Output coupling link
product type designation	3RQ3
General technical data	
display version LED	Yes
product component	
 relay output 	Yes
semi-conductor output	No
consumed active power	0.3 W
insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 rated value	300 V
surge voltage resistance rated value	4 kV
maximum permissible voltage for safe isolation	
 between control and auxiliary circuit 	300 V
percental drop-out voltage related to the input voltage	10 %
protection class IP	IP20
shock resistance	
• acc. to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
• acc. to IEC 60068-2-6	6 150 Hz: 2 g
operating frequency maximum	72 000 1/h
switching behavior	monostable
mechanical service life (switching cycles) typical	10 000 000
thermal current	6 A
reference code acc. to IEC 81346-2	K
Control circuit/ Control	
control supply voltage at DC	
rated value	24 V
operating range factor control supply voltage rated value at DC	
initial value	0.8
full-scale value	1.25
switch ON delay time	
at DC maximum	12 ms
OFF delay time	13 ms
design of the relay operating mechanism	poled

product component plug-in socket	Yes
Short-circuit protection	100
	fund aC: 4 A
design of the fuse link for short-circuit protection of the auxiliary switch required	fuse gG: 4 A
Auxiliary circuit	
type of switching contact	Changeover contact
material of switching contacts	AgSnO2-HTV
number of CO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15	
● at 24 V	3 A
● at 250 V	3 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
● at 125 V	0.2 A
• at 250 V	0.1 A
contact reliability of auxiliary contacts	one incorrect switching operation of 100 million switching operations (5 V, 1 mA)
Main circuit	
type of voltage	DC
Inputs/ Outputs	
property of the output short-circuit proof	No
Outputs	
ampacity of the output relay at AC-15 at 250 V at 50/60 Hz	3 A
ampacity of the output relay at DC-13	
● at 24 V	1 A
● at 125 V	0.2 A
● at 250 V	0.1 A
Electromagnetic compatibility	
EMC emitted interference acc. to IEC 60947-1	ambience A (industrial sector)
EMC immunity acc. to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
due to burst acc. to IEC 61000-4-4	2 kV
 due to conductor-earth surge acc. to IEC 61000-4-5 	2 kV
 due to conductor-conductor surge acc. to IEC 61000-4-5 	1 kV
field-based interference acc. to IEC 61000-4-3	10 V/m
electrostatic discharge acc. to IEC 61000-4-2	6 kV contact discharge / 8 kV air discharge
Display	
display version as status display by LED	LED green
Connections/ Terminals	
product function removable terminal	No
type of electrical connection for auxiliary and control circuit	spring-loaded terminals (push-in)
wire length	, ,
• at DC maximum	1 000 m
type of connectable conductor cross-sections	
• solid	1x (0.25 2.5 mm²)
 finely stranded with core end processing 	1x (0.25 1.5 mm²)
finely stranded without core end processing	1x (0.25 2.5 mm²)
at AWG cables solid	1 x (20 14)
at AWG cables stranded	1x (20 14)
connectable conductor cross-section solid	0.25 2.5 mm²
 connectable conductor cross-section finely stranded with core end processing 	0.25 1.5 mm²
connectable conductor cross-section finely stranded without core end processing	0.25 2.5 mm²
 AWG number as coded connectable conductor cross section solid 	20 14
 AWG number as coded connectable conductor 	20 14

cross section stranded		
Installation/ mounting/ dimensions		
mounting position	any	
fastening method	snap-on mounting	
height	93 mm	
width	6.2 mm	
depth	76 mm	
required spacing		
 with side-by-side mounting 		
— forwards	0 mm	
— backwards	0 mm	
— upwards	0 mm	
— downwards	0 mm	
— at the side	0 mm	
 for grounded parts 		
— forwards	0 mm	
— backwards	0 mm	
— upwards	0 mm	
— at the side	0 mm	
— downwards	0 mm	
 for live parts 		
— forwards	0 mm	
— backwards	0 mm	
— upwards	0 mm	
— downwards	0 mm	
— at the side	0 mm	
Ambient conditions		
installation altitude at height above sea level maximum	2 000 m	
 ambient temperature during operation 	-25 +60 °C	
 ambient temperature during storage 	-40 +85 °C	
 ambient temperature during transport 	-40 +85 °C	
relative humidity during operation	10 95 %	
Certificates/ approvals		
General Product Approval		EMC













Declaration of Conformity

Marine / Shipping

other

Miscellaneous





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RQ3118-2AM01


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RQ3118-2AM01

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RQ3118-2AM01

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RQ3118-2AM01&lang=en





last modified: 10/24/2020 ☑