



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	UPGRADER DRAWINGS	LJW	2025.07.17

















RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm


NOTE:
1.MATERIAL SPECIFICATION:
1-1.MOLDING&PICKUP COVER: HIGH TEMPERATURE MATERIAL(LCP).
1-2.HOUSING: HIGH TEMPERATURE MATERIAL(PA9T)
1-3.CONTACTS: COPPER ALLOY(C5191)
1-4.LATCH: STAINLESS STEEL(SUS301)
1-5.SHELL: STAINLESS STEEL(SUS304)
1-6.EMI SPRING: STAINLESS STEEL(SUS304)
2.PLATING SPECIFICATION:
2-1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au1u" PLATED ON THE FUNCTIONAL AREA OF CONTACT.
WELDING ZONE COATING SEE THE TABLE
2-2.SHELL:
Ni 30u" MIN. UNDER PLATED OVER ALL.
2-3.LATCH:
Ni 30u" MIN. UNDER PLATED OVER ALL.
SN 50u" PLATED ON SOLDER AREA.
2-4.EMI SPRING:
CLEAR ONLY
3.MECHANICAL PERFORMANCE,
3-1.INSERTION FORCE: 0.5~2.0kgf.
3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.
3-3.DURABILITY: 10000 CYCLES.
4.ELECTRICAL PERFORMANCE,
4-1. CURRENT RATING:3.0A
VOLTAGE RATING:5.0V
4-2.INSULATION RESISTANCE: 100MΩ MIN.
4-3.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
4-4.LOW CONTACT RESISTANCE: INITIAL 40mΩ AFTER 50mΩ
5. ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: -25°C~+85°C.
6.IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL BE MAINTAINED FOR 10 SECONDS AT 260°C.

TABLE:

PART No.	WELDING ZONE COATING
1080027/CY-001-CM0031	GOLD FLASH COATING
CY-001-CM0048	Sn:50u"

USB TYPE-C PIN ASSIGNMENTS

A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

UNITS: mm
MAT'L:
FINISH:
Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 24PIN立式贴片公头 无脚 H=11.1MM


APPD: CZN
CHKD: CZJ
DR: LJW

PART NO.: TYPE-CM-24P-H11.1SMT-00148


SCALE	SHEET	REV.
1/1	1/2	B


RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B	---	UPGRADER DRAWINGS	LJW	2025.07.17




① 产品入载带示意图







② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	300	3300

包装说明：
1. 将检验好的成品;SMT朝下放入载带底部;每卷装300PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠;
4. 装好后并封好纸箱及贴好相关标签;
（产品包装的标签，如客户有要求，请按客户要求包装出货）
5. 载带前面留6PCS空格，后面留6PCS空格
6. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
剥离角度:165° -180°

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.20	.XX°	± 0.5°
.XXX	±0.10		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

UNITS: mm
MAT'L:
FINISH:
Q'TY:

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd.

TITLE: TYPE-C 24PIN立式贴片公头 无脚 H=11.1MM

APPD: CZN
CHKD: CZJ
DR: LJW

PART NO.: TYPE-CM-24P-H11.1SMT-00148

SCALE	SHEET	REV.
1/1	2/2	B