

RoHS Compliant

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		



组装示意图


机壳与胶圈干涉建议单边0.15最小，胶圈尺寸跑上限




装配方向

开孔尺寸参考


组装外壳时需要打环保润滑油




胶圈使用尺寸参考图




plug插入深度参考图







Note:
1.Material:
1.1 Housing: LCP
1.2 Contact:C7025,t=0.15mm
1.3 Shell: SUS316
2.ELECTRICAL:
2−1:CURUENT RATAING:
VBUS AND GND CONTACTS RATED AT 1.25A
PARALLELED FOR A TOTAL OF 5A;
2−2:INITIAL CONTACT RESISTANCE :40 MEGOHMS
2−3:DIEELECTRIC WITHSTANDING VOLTAGE:
100V AC MIN;
3:MECHANICAL CHARACTERISTICS:
3−1:MATING FORCE:5~20N
3−2:UNMATING FORCE:8~20N(INITIAL),
6~20N(AFTER 10000 CYCLES)
3−3:FREQUENCE: 200±50 CYCLES /HOUR,
10000 CYCLES
3−4:OPERATING TEMPERATURE ;−40°~80°.

Suggested adsorption size



Added suction cover view





RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED ±0.05mm

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXP1	B11	SSRXP1
A3	SSTXN1	B10	SSRXN1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXN2	B3	SSTXN2
A11	SSRXP2	B2	SSTXP2
A12	GND	B1	GND

X.	±0.50	X.°	± 2°
.X	±0.30	.X°	± 1°
.XX	±0.10	.XX°	± 0.5°
.XXX	± 0.05		

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

UNITS mm
MAT'L
FINISH
Q'TY

广东创粤科技有限公司

TITLE: TYPE-C 24PIN直立式防水母座双筋位6.68 外壳粉末冶金


APPD:
CHKD:
DR:

DWG NO.: TYPE-C-24P-H6.68SMT-00151-1


SCALE	SHEET	REV.
1/1	1/1	A

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		


RoHS Compliant




① 产品入载带示意图




② 卷盘贴标签示意图



③ 7盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	500	5500

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装500PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每11盘叠;具体如图三所示
5. 装好后并封好纸箱及贴好相关标签;具体如图五所示;
   (产品包装的标签，如客户有要求，请按客户要求包装出货)
6. 载带前面留17PCS空格，后面留17PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,
   剥离角度:165°-180°

X. ±0.50	X.° ± 2°	UNITS	mm
.X ±0.30	.X° ± 1°	MAT'L	
.XX ±0.10	.XX° ± 0.5°	FINISH	
.XXX ±0.05		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

TITLE:
TYPE-C 24/16PIN直立式防水母座 粉末冶金 包规

APPD:
CHKD:
DR:

DWG NO.:
TYPE-C-24P-H6.68SMT-00151-1

SCALE	SHEET	REV.
1/1	1/1	A