

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
D				




开孔尺寸参考　　胶圈使用尺寸参考图


组装外壳时需要打环保润滑油








SECTION A-A











RECOMMENDED P.C.B. LAYOUT (T:1.00mm)

TOLERANCE UNSPECIFIED ±0.05mm


NOTES:

1.MATERIAL:
- MOLDING: LCP UL94 V-0
- CONTACT:COPPER ALLOY.
  PLATED GOLD ON CANTACT AREA,
  G/F GOLD ON SOLDER AREA,
  50u" NICKEL PLATING OVER ALL.
- SHELL: SUS304-H,T=0.30
  50u" NICKEL PLATING OVER ALL.
- EMI SHILD:SUS301-H,T=0.10
- LATCH:SUS301-H,T=0.15

2.MECHANICAL:
- INSERTION: 5~20N.
- EXTRACTION: 8~20N.
- DURABILITY: 10000 CYCLES

3.ELECTRICAL:
- CURRENT: 5A MIN FOR VBUS;
  0.25A MIN FOR OTHER.
- VOLTAGE: 5VAC MAX
- WITHSTANDING VOLTAGE: 100V AC.
- CONTACT RESISTANCE: 40mΩ MAX.
- INSULATION RESISTANCE: 100MΩ MIN.

4.ENVIRONMENTAL
- TEMPERATURE RANGE: -30°C TO +80°C



Added suction cover view

X. ±0.50	X.° ±2°	UNITS	mm
.X ±0.30	.X° ±1°	MAT'L	
.XX ±0.20	.XX° ±0.5°	FINISH	
.XXX ±0.10		Q'TY	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE: TYPE-C 24PIN 立式贴片10.0 防水母座

APPD:

CHKD:


DR:

PART NO.: TYPE-C-24P-H10.0SMT-00149


SCALE	SHEET	REV.
1/1	1/2	D

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
D				




① 产品入载带示意图




② 卷盘贴标签示意图



③ 产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	400	4400

包装说明：

1. 将检验好的成品;对插口朝前放入载带;每卷装400PCS产品
2. 将包装好的产品;每盘必须贴上内标签
3. 将贴好内标签的产品每11盘叠
4. 装好后并封好纸箱及贴好相关标签

(产品包装的标签，如客户有要求，请按客户要求包装出货)

5. 载带前面留15PCS空格，后面留15PCS空格

X. ±0.50	X.° ± 2°	UNITS	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	mm	Guangdong Chuangyue Technology Co.,Ltd
.XX ±0.20	.XX° ± 0.5°	MAT'L	TITLE: TYPE-C 24PIN 立式贴片10.0 防水母座
.XXX ±0.10		FINISH	APPD:
		Q'TY	CHKD:
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

PART NO.: TYPE-C-24P-H10.0SMT-00149

SCALE	SHEET	REV.
1/1	2/2	D