


RoHS Compliant

Process Capable

REV.	ZONE	DESCRIPTION	DESIGN	DATE
A		NEW		









RECOMMEND PCB LAYOUT(THICKNESS=1.6mm)

TOLERANCE: ±0.05





Notes:

Specifications:

1. Current rating: 1 A Max.
2. Dielectric withstanding:voltage: 100V(AC) for 1 min.
3. Contact resistance: 50m Max.
4. Insulation resistance: 100M Min.
5. Total mating force: 3.57 Kgf Max.
6. Total unmating force: 1.0 Kgf Min.0.81~2.05 Kgf Min.after 10000 insertion/extration cycles
7. Temperature range: -30°C~+80°C

MICRO USB B TYPE PIN ASSIGNMENTS

PIN NUMBER	1	2	3	4	5
SIGNAL NAME	VBUS	D-	D+	ID	GND

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司
.X ±0.30	.X° ± 1°	MAT'L	TITLE: MICRO USB 5PIN立贴母座 三脚 高度H=6.2MM 直边
.XX ±0.20	.XX° ± 0.5°	FINISH	APPD: / PART NO.: MICRO-5P-H6.2SMT-00106
.XXX ± 0.10		Q'TY	CHKD: / SCALE 1/1 / SHEET 1/1 / REV. A
			DR:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD