



RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	UPGRADE DRAWINGS	ZJ	2024.09.27
D	---	UPGRADE DRAWINGS	QDY	2026.10.28














NOTE:
1. MATERIAL SPECIFICATION:
   1-1. MOLDING&PICKUP COVER: HIGH TEMPERATURE MATERIAL(LCP).
   1-2. HOUSING: HIGH TEMPERATURE MATERIAL(PA9T)
   1-3. CONTACTS: COPPER ALLOY(C5191)
   1-4. LATCH: STAINLESS STEEL(SUS301)
   1-5. SHELL: STAINLESS STEEL(SUS304)
   1-6. EMI SPRING: STAINLESS STEEL(SUS304)
2. PLATING SPECIFICATION:
   2-1. CONTACTS:
      Ni 50u" MIN. UNDER PLATED OVER ALL.
      Au1u" PLATED ON THE FUNCTIONAL AREA OF CONTACT.
      MATTE TIN 50u" MIN. PLATED ON SOLDER AREA.
   2-2. SHELL:
      Ni 30u" MIN. UNDER PLATED OVER ALL.
   2-3. LATCH:
      Ni 30u" MIN. UNDER PLATED OVER ALL.
   2-4. EMI SPRING:CLEAR ONLY
3. MECHANICAL PERFORMANCE,
   3-1. INSERTION FORCE: 5~20N.
   3-2. REMOVAL FORCE: 8~20N;
      AFTER DURABILITY TEST:6~20N
   3-3. DURABILITY: 10000 CYCLES.
4. ELECTRICAL PERFORMANCE,
   4-1. CURRENT RATING:3.0A
      VOLTAGE RATING:5.0V
   4-2. INSULATION RESISTANCE: 100MΩ MIN.
   4-3. DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
   4-4. LOW CONTACT RESISTANCE: INITIAL 40mΩ AFTER 50mΩ
5. ENVIRONMENTAL PERFORMANCE:
   OPERATING TEMPERATURE: -40° C~+85° C.
6. IR REFLOW:
   THE PEAK TEMPERATURE ON THE BOARD SHALL
   BE MAINTAINED FOR 10 SECONDS AT 260° C.







ADDED SUCTION CAP VIEW
SCALE 1:2

PIN ASSIGNMENT											
A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND			VBUS	SBU1	D-	D+	CC1	VBUS			GND
GND			VBUS	CC2			SBU2	VBUS			GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

TOLERANCE UNSPECIFIED ±0.05mm

X. ± 0.30	X.° ± 2°
.X ± 0.25	.X° ± 1°
.XX ± 0.20	.XX° ± 0.5°
.XXX ± 0.10	

UNITS: mm

MAT'L:

FINISH:

Q'TY:

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,Ltd.

广东创粤科技有限公司
Guangdong Chuangyue Technology Co.,Ltd

TITLE: Type C 16PIN立式贴片公头 无脚 H=12.1

APPD: CZN

CHKD: Peter Tan


DR: QDY

PART NO.: TYPE-CM-16P-H12.1SMT-00156


SCALE	SHEET
1/1	1/2

RoHS Compliant


REV.	ZONE	DESCRIPTION	DESIGN	DATE
C	---	UPGRADE DRAWINGS	ZJ	2024.09.27
D	---	UPGRADE DRAWINGS	QDY	2026.10.28




① 产品入载带示意图




② 卷盘贴标签示意图



③ 11盘产品叠层示意图



④ 产品入外箱示意图



⑤ 外箱封箱示意图

	REEL	CARTON
CONNECTOR (PCS)	300	3300

包装说明：

1. 将检验好的成品;SMT朝下放入载带底部;每卷装300PCS产品;
2. 将包装好的产品;每盘必须贴上内标签;
3. 将贴好内标签的产品每11盘叠放好;
4. 装好后并封好纸箱及贴好相关标签;
(产品包装的标签，如客户有要求，请按客户要求包装出货)
5. 载带前面留6PCS空格，后面留6PCS空格

X. ± 0.30	X.° ± 2°	UNITS mm	广东创粤科技有限公司 Guangdong Chuangyue Technology Co.,Ltd
.X ± 0.25	.X° ± 1°	MAT'L	TITLE: Type C 16PIN立式贴片公头 无脚 H=12.1
.XX ± 0.20	.XX° ± 0.5°		
.XXX ± 0.10		FINISH	APPD: CZN / PART NO.: TYPE-CM-16P-H12.1SMT-00156
		Q'TY	CHKD: Peter Tan
			DR: QDY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,Ltd.

SCALE 1/1 SHEET 2/2