

3-2308350-2  ACTIVE

### Rail D-Sub Backshells

TE Internal #: 3-2308350-2

Crimp Barrel, Shielded, Rail D-Sub Backshells

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Strain Relief > Crimp Barrel for D-Sub Connectors



Strain Relief Accessory Type: **Crimp Barrel**

Shielded: **Yes**

Thread Size: **None**

Operating Temperature Range: **-40 – 90 °C [ -40 – 194 °F ]**

[All Crimp Barrel for D-Sub Connectors \(22\)](#)

## Features

### Product Type Features

Strain Relief Accessory Type	Crimp Barrel
------------------------------	--------------

### Mechanical Attachment

Thread Size	None
-------------	------

### Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

### Operation/Application

Shielded	Yes
----------	-----

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
------------------------------	---------------------------

EU ELV Directive 2000/53/EC	Not Yet Reviewed
-----------------------------	------------------

China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
---	--------------------------------------

EU REACH Regulation (EC) No. 1907/2006
--

Current ECHA Candidate List: JUNE 2023

(235)

Candidate List Declared Against: JUNE  
2023 (235)

SVHC > Threshold:  
Pb (3.5% in Component Part)

**Article Safe Usage Statements:**

Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-2308348-8  
CRIMP FLANGE 8 LARGE



TE Part # 1-2308349-9  
CRIMP FLANGE 9 SMALL



TE Part # 3-2823558-9  
CRIMP INSERTS (BARREL ID 16.0 X  
OD 17.0)

## Also in the Series | Rail D-Sub Backshells




Connector Backshells(69)




Connector Strain Relief(53)



Crimp D-Sub Connectors(10)



D-Sub Connector Contacts(5)



Insertion &amp; Extraction Tools(2)



Rectangular Connector Hardware(19)

## Customers Also Bought

TE Part #2-2308348-5  
CRIMP FLANGE 15 LARGETE Part #140814-1  
250 FASTON,TAB,BRTE Part #3-2308350-1  
CRIMP BARREL21TE Part #449582-000  
VERSAFIT-MINI-SPL-3/4-BKTE Part #371476-000  
55/0114-26-9TE Part #086427-000  
55PC0121-12-0/2TE Part #408647-000  
55PC1121-20-6/9-9TE Part #482043-000  
55PC1121-22-6/9-0TE Part #EXP5-1KPS-C00001  
XPS-X-1KPS

## Documents

### Product Drawings

[CRIMP BARREL22](#)

English

### CAD Files

[3D PDF](#)

3D

### Customer View Model

[ENG\\_CVM\\_CVM\\_3-2308350-2\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_3-2308350-2\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_3-2308350-2\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[Rail D-Sub Backshells Flyer](#)

English