



Connectors > Automotive Connectors > Automotive Housings > LEAVYSEAL Housings



Connector System: **Wire-to-Wire**
Number of Positions: **22**
Connector & Housing Type: **Housing for Female Terminals**
Centerline (Pitch): **4 mm, 6 mm [.157 in, .236 in]**
Sealable: **Yes**

[All LEAVYSEAL Housings \(64\)](#)

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Female Terminals
Sealable	Yes
Primary Locking Feature	On the Terminal

Configuration Features

Number of Positions	22
Number of Rows	3, 4

Electrical Characteristics

Operating Voltage	42 VDC
Nominal Voltage Architecture	12 V, 24 V, 42 V

Body Features

Cable Exit Angle	90°
Primary Product Color	Black
Connector & Keying Code	A



Contact Features

Contact Size	1.5K, 2.8mm
Contact Type	Receptacle
Mating Tab Width	1.6 mm, 2.8 mm[.063 in][.11 in]
Contact Current Rating (Max)	40 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	With
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PBT GF
Centerline (Pitch)	4 mm, 6 mm[.157 in][.236 in]

Dimensions

Connector Height	37 mm[1.457 in]
Product Width	42.5 mm[1.673 in]
Product Length	69.7 mm[2.744 in]
Row-to-Row Spacing	6 mm[.236 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Degree of Protection	IP67
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	180
Packaging Method	Box



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 964972-1
EINZELLEITERDICHTNG



TE Part # 828905-1
SINGLE-WIRE-SEAL(5MM HOLE)



TE Part # CAT-L489-CH8172
LEAVYSEAL Housings



TE Part # 2112452-1
COVER,FOR 22POS





TE Part # CAT-AM705-T273
AMP MCP, RECEPTACLE AND TAB



TE Part # 1823444-1
ADAPTER, FOR A-PILLAR, ASSY




TE Part # 828904-1
SINGLE WIRE SEAL FOR J.P.T.CON




TE Part # 2112452-2
COVER, FOR 22POS


Also in the Series | LEAVYSEAL




Automotive Connector Caps & Covers (17)



Automotive Housings(79)



Insertion & Extraction Tools(5)



Other Automotive Connector Accessories(15)



PCB Headers & Receptacles(16)

Customers Also Bought



TE Part #1-1734248-3
1.0 FPC, ZIF V/T, SMT, 13P



TE Part #6-2176415-0
8W STD M/OX 5% 8K2



TE Part #2-2366509-2
48POS, HYBRID, PIN HSG ASSY, SLD, COD B



TE Part #2-2366509-3
48POS, HYBRID, PIN HSG ASSY, SLD, COD C



TE Part #2-2366509-4
48POS, HYBRID, PIN HSG ASSY, SLD, COD D



TE Part #2366494-2
48POS, HYBRID, SOC HSG ASSY, SLD, COD B



TE Part #2366494-3
48POS, HYBRID, SOC HSG ASSY, SLD, COD C



TE Part #2366494-4
48POS, HYBRID, SOC HSG ASSY, SLD, COD D



TE Part #2366509-2
48POS, HYBRID, PIN HSG ASSY, SLD,
COD B



TE Part #C616253001
55E0219-0.75-9(B01)

Documents

Product Drawings

22POS, MIXED, REC HSG, ASSY, SEALED

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1823440-3_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1823440-3_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1823440-3_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

German