
B772 TRANSISTOR（PNP）

SOT-89-3L



1. BASE
2. COLLETOR
3. EMITTER

FEATURE

- Low speed switching

MAXIMUM RATINGS (T_a=25℃ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{CBO}	Collector-Base Voltage	-40	V
V_{CEO}	Collector-Emitter Voltage	-30	V
V_{EBO}	Emitter-Base Voltage	-6	V
I_C	Collector Current -Continuous	-3	A
P_C	Collector Power Dissipation	0.5	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	250	℃/W
T_J,T_{stg}	Operation Junction and Storage Temperature Range	-55~150	℃

ELECTRICAL CHARACTERISTICS (T_a=25℃ unless otherwise specified)


Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	I_C=-100μA ,I_E=0	-40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	I_C= -10mA , I_B=0	-30			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	I_E= -100μA,I_C=0	-6			V
Collector cut-off current	I_{CBO}	V_{CB}= -40V, I_E=0			-1	μA
Collector cut-off current	I_{CEO}	V_{CE}=-30V, I_B=0			-10	μA
Emitter cut-off current	I_{EBO}	V_{EB}=-6V, I_C=0			-1	μA
DC current gain	h_{FE}	V_{CE}= -2V, I_C= -1A	60		400	
Collector-emitter saturation voltage	$V_{CE(sat)}$	I_C=-2A, I_B= -0.2A			-0.5	V
Base-emitter saturation voltage	$V_{BE(sat)}$	I_C=-2A, I_B= -0.2A			-1.5	V
Transition frequency	f_T	V_{CE}= -5V, I_C=-0.1A f =10MHz	50			MHz

CLASSIFICATION OF h_{FE}


Rank	R	O	Y	GR
Range	60-120	100-200	160-320	200-400

Typical Characteristics


Static Characteristic




h_{FE} — I_C




V_{CEsat} — I_C




V_{BEsat} — I_C




I_C — V_{BE}




f_T — I_C



P_C — T_a




SOT-89-3L Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

SOT-89-3L Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:±0.05mm.
3.The pad layout is for reference purposes only.