







SECTION A–A
SCALE 2:1





BOARDLOCK TYPE

TAB TYPE

				TOLERANCE	
				LINEAR	ANGLES
				X.±0.40	X°.±
				.X±0.30	.X°±
A	E2611001	Lin xuejun	Nov,02,2026	.XX±0.20	.XX°±
REV	ECN NO.	NAME	DATE	.XXX±0.10	.XXX°±

UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED

APPD:	Schumi	MAT'L:	
CHKD:	Lei songping	FINISH:	
DRWN:	Li xiaqin	Q'TY:	

TITLE: DDR 4, VERTICAL
288P MEMORY SOCKET SMT TYPE

PART NO.	90411-XXXXXX
DWG NO.	C-90411

UNITS	SCALE	SHEET	REV
MM	1 : 1	1 OF 5	A

CUSTOMER

NOTES:

1. MATERIAL :
   - 1.1 HOUSING: PA9T, HF, UL94 V-0, COLOR: SEE PART NO..
   - 1.2 LATCH: PA9T, HF, UL94 V-0, COLOR: SEE PART NO..
   - 1.3 CONTACTS: COPPER ALLOY.
   - 1.4 BOARDLOCKS AND TAB: SUS.

2. FINISH :
   - 2.1 CONTACT
     [SEE PART NO..] GOLD PLATING ON THE CONTACT AREA.
     100u" MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.
     50u" MIN. NICKEL UNDERPLATING OVERALL.

3. PART NO..

90411- XX X X X X


CONTACT AREA PLATING
- 15: 15u" Au
- 30: 30u" Au

HOUSING COLOR
- 1: BLACK
- 2: NATURAL
- 3: BLUE
- 6: YELLOW

LATCH COLOR
- 1: BLACK
- 2: NATURAL
- 3: BLUE

LATCH TYPE
- 1: SHORT LATCH
- 2: LONG LATCH
- 3: MIDDLE LATCH

BOARDLOCK TYPE
- BLANK:BOARDLOCK
- 1:TAB



DIM "B"	DIM "A"	LATCH TYPE
148.8	162.0	LONG
144.2	156.0	MIDDLE
142.3	152.0	SHORT

TOLERANCE	
LINEAR	ANGLES
X.±0.40	X°.±
.X±0.30	.X°±
.XX±0.20	.XX°±
.XXX±0.10	.XXX°±

UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED

APPD:	Schumi	MAT'L:	
CHKD:	Lei songping	FINISH:	
DRWN:	Li xiaqin	Q'TY:	

TITLE: DDR 4, VERTICAL 288P MEMORY SOCKET SMT TYPE


PART NO. 90411-XXXXXX

DWG NO. C-90411


UNITS	SCALE	SHEET	REV
MM	1 : 1	2 OF 5	A

	SEE SHEET 1		
REV	ECN NO.	NAME	DATE

CUSTOMER




RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 BOARDLOCKS



RECOMMENDED PCB LAYOUT (TOP VIEW)
FOR 3 TABS



RECOMMENDED PCB LAYOUT (TOP VIEW)



DETAIL A
SCALE 2:1

TOLERANCE	
LINEAR	ANGLES
X.±0.40	X°.±
.X±0.30	.X°±
.XX±0.20	.XX°±
.XXX±0.10	.XXX°±

UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED

APPD: Schumi	MAT'L:
CHKD: Lei songping	FINISH:
DRWN: Li xiaqin	Q'TY:


TITLE: DDR 4, VERTICAL
288P MEMORY SOCKET SMT TYPE

PART NO.	90411-XXXXXX
DWG NO.	C-90411

UNITS	SCALE	SHEET	REV
MM	1 : 1	3 OF 5	A

	SEE SHEET 1			
REV	ECN NO.	NAME	DATE	

CUSTOMER



TOLERANCE	
LINEAR	ANGLES
X.±0.40	X°.±
.X±0.30	.X°±
.XX±0.20	.XX°±
.XXX±0.10	.XXX°±

UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED

APPD: Schumi	MAT'L:
CHKD: Lei songping	FINISH:
DRWN: Li xiaqin	Q'TY:

TITLE: DDR 4, VERTICAL 288P MEMORY SOCKET SMT TYPE


PART NO. 90411-XXXXXX

DWG NO. C-90411

UNITS	SCALE	SHEET	REV
MM	1 : 1	4 OF 5	A


REV	ECN NO.	NAME	DATE
	SEE SHEET 1		


CUSTOMER



NOTES :

1. MATERIAL :
   TRAY: HIPS, COLOR: BLACK.
   BOX: CORRUGATED FIBER
   TRANSPARENT BAG: PE, SIZE: 660mm*600mm*0.08mm





PCS/ TRAY	TRAY/ BOX	PCS/ BOX	NET WEIGHT	GROSS WEIGHT
24	20	480	2.55 KG	5.75 KG

TOLERANCE	
LINEAR	ANGLES
X.±0.40	X°.±
.X±0.30	.X°±
.XX±0.20	.XX°±
.XXX±0.10	.XXX°±

UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED

APPD:	Schumi	MAT'L:	
CHKD:	Lei songping	FINISH:	
DRWN:	Li xiaqin	Q'TY:	

TITLE: DDR 4, VERTICAL 288P MEMORY SOCKET SMT TYPE

PART NO. 90411-XXXXXX

DWG NO. C-90411

UNITS	SCALE	SHEET	REV
MM	1 : 1	5 OF 5	A

	SEE SHEET 1			
REV	ECN NO.	NAME	DATE	

CUSTOMER