



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **4.2 mm [.165 in]**

Features

Product Type Features

Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	4
PCB Mount Orientation	Vertical
Number of Power Positions	0
Number of Signal Positions	4
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
----------------	--------



Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	13 A
Contact Retention Within Housing	With
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 μm[80 μin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Retention	With
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention Type	Latch
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	4.2 mm[.165 in]
Housing Color	White
Housing Material	Nylon GF

Dimensions

Connector Height	12.8 mm[.504 in]
Product Width	9.8 mm[.386 in]
Wire Size	.12 – 1.4 mm²
Row-to-Row Spacing	4.2 mm[.165 in]

Usage Conditions

Operating Temperature Range	-40 – 221 °C[-40 – 105 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Circuit Identification Feature	With
--------------------------------	------



Industry Standards

CSA Rating	208567
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	375
Packaging Method	Box & Tray, Tray

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2825261-0
20P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 2-2825261-4
24P VAL-U-LOK HCS VRT HDR W/P V0




TE Part # 2825261-2
2P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 2825261-6
6P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 2825261-8
8P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 1-2825261-0
10P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 1-2825261-2
12P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 1-2825261-4
14P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 1-2825261-6
16P VAL-U-LOK HCS VRT HDR W/P V0



TE Part # 2-2825261-2
22P VAL-U-LOK HCS VRT HDR W/P V0

Customers Also Bought




TE Part #6-2176070-3
3521 3K9 1% 2W




TE Part #293735-1
4 pos. coverpart (kit) for P/N 794616-4




TE Part #293734-1
4 pos. coverpart (kit) for P/N 794617-4



TE Part #2029181-3
3P VAL-U-LOK VRTHDR W/PGS GW




TE Part #1-1586040-6
16P VAL-U-LOK VRT HDR W/P V0



TE Part #2029054-5
5P VAL-U-LOK SR HDR SN V2 W/DH



TE Part #2825261-8
8P VAL-U-LOK HCS VRT HDR W/P V0



TE Part #7-6474640-6
FSN-23A



Documents

Product Drawings

4P VAL-U-LOK HCS VRT HDR W/P V0

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2825261-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2825261-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2825261-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English