
TK2N7002K

60V N-Channel MOSFET


Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
60V	0.9Ω@10V	0.34A
	1.1Ω@4.5V	

SOT-23



Schematic diagram




Feature

- Trench Technology Power MOSFET
- Low $R_{DS(ON)}$
- Low Gate Charge
- ESD Protected

Application

- Load Switch
- DC/DC Converter

MARKING:



ABSOLUTE MAXIMUM RATINGS (T_A = 25℃ unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain - Source Voltage		V_{DS}	60	V
Gate - Source Voltage		V_{GS}	±20	V
Continuous Drain Current[1,5]	T_A = 25℃	I_D	0.34	A
Pulsed Drain Current[2]		I_{DM}	1.0	A
Power Dissipation[4,5]	T_A = 25℃	P_D	0.35	W
Thermal Resistance from Junction to Ambient[5]		$R_{\theta JA}$	357	℃/W
Junction Temperature		T_J	150	℃
Storage Temperature		T_{STG}	-55~ +150	℃

MOSFET ELECTRICAL CHARACTERISTICS (T_J = 25℃ unless otherwise noted)

Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Off Characteristics						
Drain - Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0V, I_D = 250μA	60			V
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 48V, V_{GS} = 0V			1	μA
Gate - Body Leakage Current	I_{GSS}	V_{GS} = ±20V, V_{DS} = 0V			±5	μA
On Characteristics[3]						
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250μA	1	1.5	2.5	V
Drain-source On-resistance	$R_{DS(on)}$	V_{GS} = 10V, I_D = 0.3A		0.9	2.5	Ω
		V_{GS} = 4.5V, I_D = 0.2A		1.1	3	
Dynamic Characteristics						
Input Capacitance	C_{iss}	V_{DS} = 30V, V_{GS} = 0V, f = 1MHz		23.7		pF
Output Capacitance	C_{oss}			5.3		
Reverse Transfer Capacitance	C_{rss}			2.5		
Gate Resistance	R_g	V_{DS} = 0V, V_{GS} = 0V, f = 1MHz		160		Ω
Switching Characteristics						
Total Gate Charge	Q_g	V_{DS} = 30V, V_{GS} = 10V, I_D = 0.3A		0.29		nC
Gate-source Charge	Q_{gs}			0.23		
Gate-drain Charge	Q_{gd}			0.12		
Turn-on Delay Time	$t_{d(on)}$	V_{DD} = 30V, V_{GS} = 10V, R_L = 100Ω, R_G = 3Ω		3.5		ns
Turn-on Rise Time	t_r			3.2		
Turn-off Delay Ttime	$t_{d(off)}$			12		
Turn-off Fall Time	t_f			10		
Source - Drain Diode Characteristics						
Diode Forward Voltage[3]	V_{SD}	V_{GS} = 0V, I_S = 0.3A			1.2	V

Notes :

1.The maximum current rating is limited by package.

2.Pulse Test : Pulse Width ≤ 10μs, duty cycle ≤ 1%.


3.Pulse Test : Pulse Width ≤ 300μs, duty cycle ≤ 2%.

4.The power dissipation P_D is limited by $T_{J(MAX)}$ = 150°C.


5.Device mounted on 1in^2 FR-4 board with 2oz. Copper, in a still air environment with T_A =25°C.

Typical Characteristics


Output Characteristics




Transfer Characteristics




$R_{DS(ON)}$ — I_D





$R_{DS(ON)}$ — V_{GS}




I_S — V_{SD}










Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

SOT-23 Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:± 0.05mm.
3.The pad layout is for reference purposes only.