



Connectors > Rectangular Connectors > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Gold**
Contact Size: **Size 16**
Wire Size: **20 – 16 AWG**

Features

Contact Features

Contact Type	Socket
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold
Contact Size	Size 16
Contact Current Rating (Max)	13 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Dimensions

Wire Size	.5 – 1.5 mm²
-----------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233)



SVHC > Threshold:
Pb (1.2% in Contact Lead-Copper Alloy)













Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>











Compatible Parts

 <p>TE Part # YDIV40E25-37SAV001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SAC001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SBV001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SBC001 RECP ASSY</p>
 <p>TE Part # YDIV40E25-37SCV001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SCC001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SDV001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SDC001 RECP ASSY</p>
 <p>TE Part # YDIV40E25-37SNV001 RECP ASSY</p>	 <p>TE Part # YDIV40E25-37SNC001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SAV001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SAC001 RECP ASSY</p>



 <p>TE Part # YDIV40G25-37SBV001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SBC001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SCV001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SCC001 RECP ASSY</p>
 <p>TE Part # YDIV40G25-37SDV001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SDC001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SNV001 RECP ASSY</p>	 <p>TE Part # YDIV40G25-37SNC001 RECP ASSY</p>

Customers Also Bought

 <p>TE Part #38941-22L CONTACTS</p>	 <p>TE Part #YDTS20W25-61ANV001 RECP ASSY</p>	 <p>TE Part #38941-16 CONTACTS</p>	 <p>TE Part #38941-12L CONT PIN</p>
 <p>TE Part #YDIV46E23-35PNC003 PLUG ASSY</p>	 <p>TE Part #6162-284-0877 CONT SOC ASSY</p>	 <p>TE Part #38941-16L CONT PIN</p>	 <p>TE Part #59101WJ20PN-18 PLUG ASSY</p>
 <p>TE Part #72531-21-41PN HERM RECP</p>	 <p>TE Part #499725-000 D-621-0011CS1271</p>		

Documents



Product Drawings

CONT SOC ASSY

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_38943-16L_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_38943-16L_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_38943-16L_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.