

2350943-1

✓ ACTIVE

DEUTSCH | DEUTSCH NTSEAL

TE Internal #: 2350943-1


Panel Mount Flange, VMQ, Yellow, -40 – 125 °C [-40 – 257 °F]

Operating Temperature, DEUTSCH NTSEAL

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Panel Mount Flange**

Primary Product Material: **VMQ**

Primary Product Color: **Yellow**

Operating Temperature (Max): **125 °C [ 257 °F ]**

Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**

## Features

### Product Type Features

Connector Seal & Plug Type

Panel Mount Flange

### Body Features

Primary Product Material

VMQ

Primary Product Color

Yellow

### Usage Conditions

Operating Temperature (Max)

125 °C[257 °F]

Operating Temperature Range

-40 – 125 °C[-40 – 257 °F]

## Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023  
(235)

Candidate List Declared Against: JUNE  
2023 (235)  
Does not contain REACH SVHC

#### Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free

#### Solder Process Capability

Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1-2350891-1  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD A



TE Part # 1-2350891-2  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD B




TE Part # 1-2350891-3  
20POS, HYBRID, PIN HSG, SLD, COD C



TE Part # 1-2350891-4  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD D



TE Part # 2-2350891-1  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD A



TE Part # 2-2350891-2  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD B




TE Part # 2-2350891-3  
20POS, HYBRID, PIN HSG, SLD, COD C




TE Part # 2-2350891-4  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD D

## Also in the Series | DEUTSCH NTSEAL




Automotive Housings(37)



Connector Backshells(5)



Connector Seals &amp; Cavity Plugs(2)

Other Automotive Connector  
Accessories(5)

## Customers Also Bought

TE Part #3-1418883-1  
62.POS.MIXED REC.HSGTE Part #2350890-1  
20POS, HYBRID, SOC HSG ASSY, SLD,  
COD ATE Part #SRK06-MDA-32A-001  
PLG, 32P, BLK, E, ATE Part #2137740-1  
High-Voltage HeaderTE Part #2-2350891-4  
20POS, HYBRID, PIN HSG ASSY, SLD,  
COD DTE Part #2-2366509-1  
48POS, HYBRID, PIN HSG ASSY, SLD,  
COD ATE Part #2357302-2  
BACKSHELL,CONN KITTE Part #2357921-1  
BACKSHELL,CONN KITTE Part #2378521-1  
BACKSHELL,CONN KIT

## Documents

### Product Drawings

#### FIX RING,CONN KIT

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.3d\\_jgs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_2350943-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

[Application Specification](#)

English