



Connectors > RF Connectors > RF Connector Accessories > RF Connector Hardware



RF Connector Hardware Type: Insulating Bushing

Features

Product Type Features

RF Connector Hardware Type	Insulating Bushing
----------------------------	--------------------

Body Features

Insulating Bushing Material	Nylon
Insulating Bushing Outside Diameter	14.86 mm[.585 in]

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-329632-2
LOCKWASHER, PLATED



TE Part # 1-329631-2
JAM NUT, PLATED

Customers Also Bought



TE Part #1-487545-2
FFC Receptacle Housing: 1.27mm



TE Part #1-487547-1
FFC,RCPT CONTACT,.050\" CNTRLIN



TE Part #487378-3
2.54mm FFC Connectors Receptacle Housing



TE Part #5-6609107-8
PS0S0SS6B=C1117



TE Part #2-1609089-7
20ERK1=F4342

Documents

Product Drawings
PANEL INSULATING BUSHING
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_227223-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_227223-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_227223-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

BNC Connectors

English

Product Environmental Compliance

TE Material Declaration

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English