FOSAN TECHNOLOGY 富捷科技

Product Datasheet
产品规格说明书

FRV Series
High Voltage Thick Film Chip Resistor
高压厚膜片式电阻器

安徽省富捷电子科技有限公司
ANHUI FOJAN ELECTRONICS TECHNOLOGY CO., LTD
安徽省马鞍山市郑蒲港新区金蒲电子产业园
JINPU ELECTRONIC INDUSTRIAL PARK, ZHENGPU PORT NEW DISTRICT, MAANSHAN CITY, ANHUI PROVINCE
zoey@fosan.net.cn www.fosan.vip

高压厚膜片式电阻器
High Voltage Thick Film Chip Resistor FRV Series



■ 特点 (Features)

- 高电压 - High voltage
- 电性能稳定，可靠度高 - Stable electrical capability and high Reliability
- 符合 RoHS 指令要求 - Compliant with RoHS directive
- 符合无卤素要求 - Halogen free requirement
- 体积小，重量轻 - Miniature and light weight

■ 应用 (Application)


- 广泛应用于相机闪光灯电路、计算机、打印设备、电池充电器、汽车设备、电源电路、光盘驱动器等。
- Widely used in Camera Flash Circuit, Computer, Printer, Battery Charger, Automotive, Power supply, CD-ROM etc

■ 产品料号 (Parts Number Explanation)

示例：FRV1206F1001TS

F 公司	RV 产品别	1206 尺寸	F 公差	1001 字码	T 包装别	S 端电极	特殊码
FOJAN	**RV: High Voltage** Others series refer to Catalogue	0603 0805 1206 1210 1218 1812 2010 2512	D:±0.5% F:±1% J:±5%	±5%: 3-digits+blank 102=1KΩ 1R0=1Ω ±1%&Below: 4-digits 1001=1KΩ 1R00=1Ω	T: 7 inch reel Q:10 inch reel R:13 inch reel B:Bulk	S: Sn C: Cu A: Au	Blank: none
Company	Type	Size	Tolerance	Resistance	Packaging	Termination	Special Case


▪ 电阻结构 (Construction)



NO.	结构 Construction	主要材料 Major material
1	陶瓷基板 Ceramic substrate	三氧化二铝 Al_2O_3
2	导电层 Conductive layer(Top)	银 Ag
3	侧电极 Side conductive layer	镍铬合金 NiCr
4	阻体层 Resistive layer	氧化钌 RuO_2
5	内保护层 Inner protective layer	玻璃 Glass
6	外保护层 Outer Protective layer	环氧树脂 Epoxy
7	文字 Marking	环氧树脂 Epoxy
8	镍电极 Ni plating layer	镍 Ni
9	锡电极 Sn plating layer	锡 Sn
10	导电层 Conductive layer(Back)	银 Ag

▪ 尺寸 (Dimension):

尺寸 Dimension



单位 (unit)：mm

型别 (Type)		L	W	H	T1	T2
英制	公制					
0603	1608	1.60±0.10	0.80±0.10	0.45±0.10	0.25±0.15	0.25±0.15
0805	2012	2.00±0.10	1.25±0.10	0.50±0.10	0.35±0.20	0.40±0.20
1206	3216	3.10±0.10	1.60±0.10	0.55±0.10	0.45±0.20	0.45±0.20
1210	3225	3.10±0.10	2.50±0.15	0.55±0.10	0.45±0.15	0.50±0.20
1812	4532	4.50±0.20	3.10±0.20	0.55±0.10	0.55±0.20	0.70±0.20
2010	5025	5.00±0.10	2.50±0.15	0.55±0.10	0.45±0.15	0.50±0.20
2512	6432	6.35±0.10	3.10±0.15	0.55±0.10	0.60±0.20	0.90±0.20

■ 电气特性 (Electrical characteristics)

型别 Type	70°C 下额定功率 Rated Power at 70°C	最大工作电压 Max Working Voltage	最大过负荷电压 Max Overload Voltage	绝缘耐压 Dielectric Withstanding Voltage
0603	1/10W	350V	500V	300V
0805	1/8W	400V	800V	500V
1206	1/4W	500V	1000V	500V
1210	1/2W	500V	1000V	500V
1812	3/4W	500V	1000V	500V
2010	3/4W	500V	1000V	500V
2512	1W	500V	1000V	500V

备注（Remark）： 额定电压计算公式（The rated voltage is calculated by the following formula）：

E= $\sqrt{RP}$

E：额定电压（Rated Voltage） (V)


P：额定功率（Rated Power ） (W)

R：电阻阻值（Resistance ） (ohm)

如果计算出的电压超过此型别的最大工作电压，则此型别的最大工作电压为此电阻的额定电压。

In case the value calculated by the formula exceed the maximum working voltage as above table , the maximum working voltage shall be regarded as rated voltage.

■ 功率衰减曲线 (Derating Curve)


使用温度范围 Temperature usage range	-55℃~+155℃
说明 Describe	周围温度若超过 70℃至 155℃之间,功率可照下图曲线予以修订 If the ambient temperature exceeds 70°C to 155°C,the power can be revised according to the curve in the following figure
功率衰减曲线图 Power Attenuation Curve	

■ 温度系数 (Temperature Coefficient)

型别 Type	阻值范围 Resistance Range	产品精度和温漂系数（ppm/°C）Resistance Tolerance and TCR（ppm/°C）		
		±1%	±2%	±5%
0603/0805 1206/1210 1812/2010/2512	1Ω≤R＜10Ω	±400	±400	±400
	10Ω≤R＜1MΩ	±100	±100	±100
	1MΩ≤R＜20MΩ	±200	±200	±200

■ 性能（Performance）

内容 Item	测试方法 Test Methods	测试条件 Test Conditions	规格 Specification
温度系数 Temperature Coefficient	JIS C 5201 4.8	TCR=（R-R_0）/（t-t_0）R_0 ×10^6（ppm） R0：电阻在室温下的阻值(resistance at room temperature) R: 电阻在 125℃或-55℃下的阻值(resistance at 125℃ or -55℃) t0：室温(room temperature) t：测试温度（test temperature 125℃ or -55℃)	As SEPC
短时间过负荷 Short-time overload	JIS C 5201 4.13	加载 2.5 倍的额定电压，时间 5 秒后测量试验前后的阻值变化率。 Applied 2.5 times of rated voltage for 5 second. Measure the variation of resistance.	1%:±(1.0%+0.05Ω) 2%，5%：±(2.0%+0.05Ω)
焊锡性 Solderability	JIS C 5201 4.17	沾助焊剂后浸入锡炉，锡炉温度245±5℃，时间 3±0.5 秒。 Dip the terminal in a flux and then dip into a soldering bath at 245±5℃ for 3±0.5sec.	上锡面积＞95% (＞95% coverage)
抗焊锡热 Resist to soldering heat	JIS C 5201 4.18	沾助焊剂后浸入锡炉，锡炉温度260±5℃，时间 10±0.5 秒，测量试验前后的阻值变化率。 Dip the terminal in a flux and then dip into a soldering bath at 260±5℃ for 10±0.5sec. Measure the variation of resistance.	±(1.00% +0.05Ω)
绝缘电阻 Insulation resistance	JIS C 5201 4.6	电阻本体上加载绝缘耐压 60±5 秒后，测量绝缘阻抗。 Applied the dielectric withstanding voltage on the center of body for 60±5seconds. Then measure insulation resistance.	＞10GΩ
绝缘耐压 Dielectric withstanding voltage	JIS C 5201 4.7	电阻本体上加载绝缘耐压 60±5 秒。 Applied the dielectric withstanding voltage on the center of body for60±5seconds.	无击穿、飞弧及可见机械性损伤 No evidence of flash over, mechanical damage arcing or insulation breakdown
温度快速变化 Rapid temperature changes	JIS C 5201 4.19	电阻放入温度循环机中，T1 温度：-55±3℃；T2 温度：155±3℃./125±3℃，放置 30 分钟，共 300 个循环。量测试验前后阻值变化率. Put specimen in a chamber which temperature can be T1： -55±3℃；T2： 155±3℃/125±3℃, 30min， repeated 300 cycles. Measure the variation of resistance.	1%:±(1.0%+0.05Ω) 2%，5%：±(2.0%+0.05Ω)
温湿循环 Moisture resistance	MIL-STD-202 METHOD 106	25°C~65°C,90~100%RH, 2.5 小时; 65°C 90~100%RH, 3 小时; 65°C~25°C,80~100%RH,2.5 小时,10 个循环,试验结束 24±4 小时后进行测试. 25°C~65°C,90~100%RH, 2.5H; 65°C 90~100%RH, 3H; 65°C~25°C 80~100%RH, 2.5H, 10 cycles, Measurement at 24±4 hours after test conclusion.	1%:±(1.0%+0.05Ω) 2%，5%：±(2.0%+0.05Ω)

内容 Item	测试方法 Test Methods	测试条件 Test Conditions	规格 Specification
端子弯曲 Terminal bending	JIS C 5201 4.33	电阻焊接在测试板上进行弯折,弯折保持时间 20± 1 秒，1206(含) 以下的尺寸弯曲 5 +0.2/0 mm; 1206 以上的尺寸弯曲 2 +0.2/0 mm; 量测试验前后阻值变化率 Specimen shall be mounted on test board, then bend the board and maintained for 20± 1s. the distance of bending is 5 +0.2/0 mm for resistors which size no larger than 1206 or 2 +0.2/0 mm which size larger than 1206. Measure the variation of resistance. 测试板（test board） 压头（jig） 	±(1.00% +0.05Ω)
耐湿特性 Humidity	JIS C 5201 4.24	电阻放入恒温恒湿箱，温度 40±2℃，湿度 90~95 %RH;通电额定电压 1.5 小时，断电 0.5 小时; 重复通断电至试验时间 1000 $^{+48}/_{-0}$ 小时. 量测试验前后阻值变化率. Put the specimen in a chamber at 40±2℃ temperature and 90~95% relative humidity, then applied rated voltage for1.5H “ON” and 0.5H “OFF” repeatedly till total test time is 1000$^{+48}/_{-0}$ H. Measure the variation of resistance.	1%:±(1.0%+0.05Ω) 2%，5%：±(2.0%+0.05Ω)
负荷寿命 Load life	JIS C 5201 4.25.1	电阻放入恒温箱中，温度 70±2℃，ON TIME:1.5H，OFF TIME:0.5H，通电额定电压 1000 $^{+24}/_{-0}$小时，量测试验前后阻值变化率. Put the specimen in a chamber at 70±2℃ temperature, ON TIME:1.5H ， OFF TIME:0.5H，and applied rated voltage for 1000 $^{+24}/_{-0}$H. Measure the variation of resistance.	1%:±(1.0%+0.05Ω) 2%，5%：±(2.0%+0.05Ω)

▪ 本体标识（Marking on the Resistor's Body）

1.公差±5%的产品，以三字码标示，前两位表示阻值的有效数字，最后一位表示 10 的乘幂

±5% tolerance product: the marking is 3 digits, the first 2 digits are significant figures of resistance value and the 3rd one denotes the power number of 10, (10X)

2. ±0.5%，±1%，±2%的产品，以四字码标示，前三 位表示阻值的有效数字，最后一位表示 10 的乘幂

±0.5%, ± 1%, ±2% tolerance product: the marking is 4 digits, the first 3 digits are significant figures of resistance value and the 4th one denotes the power number of 10, (10X)

3.0603 ±1% E96 系列的标准阻值，因电阻本体太小，采用三位代码标示。

Standard E96 series values of 0603 ±1%: due to the small size of the resistor’ s body, use 3digits code to indicate the resistance value.

	**472 =47×10² =4.7KΩ**
	**10Ω以下标示：5R6 =5.6Ω** **Below 10Ω: 5R6 =5.6Ω**
	**4992 =499×10² =49.9KΩ**
	**100Ω以下标示** **6R81 =6.81Ω** **Below 100Ω: 6R81 =6.81Ω**

▪ 0603± 1% E96 系列电阻值代码 Standard E96 Series Resistance Value Code for 0603 ± 1% Marking

代码 Code	阻值 Value	代码 Code	阻值 Value	代码 Code	阻值 Value	代码 Code	阻值 Value	代码 Code	阻值 Value	代码 Code	阻值 Value
01	100	**17**	147	**33**	215	**49**	316	**65**	464	**81**	681
02	102	**18**	150	**34**	221	**50**	324	**66**	475	**82**	698
03	105	**19**	154	**35**	226	**51**	332	**67**	487	**83**	715
04	107	**20**	158	**36**	232	**52**	340	**68**	499	**84**	732
05	110	**21**	162	**37**	237	**53**	348	**69**	511	**85**	750
06	113	**22**	165	**38**	243	**54**	357	**70**	523	**86**	768
07	115	**23**	169	**39**	249	**55**	365	**71**	536	**87**	787
08	118	**24**	174	**40**	255	**56**	374	**72**	549	**88**	806
09	121	**25**	178	**41**	261	**57**	383	**73**	562	**89**	825
10	124	**26**	182	**42**	267	**58**	392	**74**	576	**90**	845
11	127	**27**	187	**43**	274	**59**	402	**75**	590	**91**	866
12	130	**28**	191	**44**	280	**60**	412	**76**	604	**92**	887
13	133	**29**	196	**45**	287	**61**	422	**77**	619	**93**	909
14	137	**30**	200	**46**	294	**62**	432	**78**	634	**94**	931
15	140	**31**	205	**47**	301	**63**	442	**79**	649	**95**	953
16	143	**32**	210	**48**	309	**64**	453	**80**	665	**96**	976

▪0603± 1%标记的倍增码 Multiplier Code for 0603 ± 1% Marking

代码 Code	Y	X	A	B	C	D	E	F
指数 Multiplier	10^{-2}	10^{-1}	10^{0}	10^{1}	10^{2}	10^{3}	10^{4}	10^{5}

阻值标示如下(So the resistance value are marked as the following examples)



10D = 124×10^{3} = 124KΩ



38Y = 243×10^{-2} = 2.43Ω

0603 ±1%的产品，在标准 E24 系列中，但不属于 E96 系列，标示与 5%的字码相同，但是在中间字码下加一条线（Standard E24 and not belong to E96 series values of 0603 ±1%, the marking is the same as 5% tolerance but marking as underline)




331 = 33×10^{1} = 330Ω




560 = 56×10^{0} = 56Ω

■ 焊接 (soldering)

- 建议回流焊曲线（Recommend reflow soldering profile)



- 建议波峰焊曲线（Recommend wave soldering profile)




- 手工焊温度（hand soldering temperature)

烙铁温度 350±10℃ 3 秒之内，避免烙铁接触电阻本体

The iron temperature is 350±10℃, hand soldering time less than 3S. Avoid solder iron tip direct touch the components body

■ 包装规格（Tapping Specification）




-卷盘尺寸（Reel dimension）

Type	Size		Unit	A	B	C	F	E
0603/0805/1206/1210	7″	5K/Reel	mm	178±2.0	60.0±1.0	13.5±0.5	11.4±0.1	9.00±0.3
0603/0805/1206	10″	10K/Reel	mm	254±2.0	100.0±1.0	13.5±0.5	11.4±0.1	9.00±0.3
0603/0805/1206	13″	20K/Reel	mm	330±2.0	100.0±1.0	13.5±0.5	11.4±0.1	9.00±0.3
1812/2010/2512	7″	4K/Reel	mm	178±2.0	60.0±1.0	13.5±0.5	15.4±1.0	13.0±0.3

-包装尺寸（packing dimension）


纸带编带 Paper Taping



Unit: mm

Dim	A	B	D	F	P0	P1	P2	W	T
0603	1.10±0.10	1.90±0.10	1.50±0.10	3.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	8.00±0.20	0.60±0.03
0805	1.65±0.20	2.40±0.20	1.50±0.10	3.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	8.00±0.20	0.75±0.05
1206	1.90±0.20	3.50±0.20	1.50±0.10	3.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	8.00±0.20	0.75±0.05
1210	2.80±0.20	3.50±0.20	1.50±0.10	3.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	8.00±0.20	0.75±0.05

塑料带编带 Embossed Taping




Unit: mm

Dim	B0	A0	D0	F	P0	P	P1	W	K0
1812	3.52±0.10	5.10±0.10	1.50±0.10	5.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	12.0 ±0.10	0.78±0.10
2010	2.75±0.10	5.40±0.10	1.50±0.10	5.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	12.0 ±0.10	0.75±0.10
2512	3.35±0.10	6.70±0.10	1.50±0.10	5.50±0.05	4.00±0.10	4.00±0.10	2.00±0.05	12.0 ±0.10	0.75±0.10

▪ 上胶带剥离力测试（Peel force of top cover tape）


上胶带以 300mm/分钟的速度，沿 165∽180 度角的方向进行剥离，如下图所示。纸带的剥离力范为 10g∽70g;
载带的剥离力范围 30∽100g。

The top cover tape is pulled at a speed of 300 mm/min with the angle between the tape during peel and the direction of unreeling maintained at 165 to 180 degree as following picture. The peel force of paper carrier tape shall be 0.1N to 0.7N(10 to 70 g), the peel force of plastic carrier tape shall be 0.3N to 1N (30 to 100 g)



▪ 建议焊盘尺寸（Recommended Pad Dimensions）

Land pattern / Type	Dimensions（mm）		
	A	B	C
0603	0.80~1.10	2.00~2.50	0.80~1.00
0805	1.00~1.40	2.90~3.40	1.00~1.40
1206	2.00~2.40	4.10~4.60	1.50~1.80
1210	2.00~2.40	4.10~4.60	2.50~3.00
1812	2.80~3.30	5.00~6.00	3.00~3.50
2010	3.40~3.90	5.70~6.50	2.50~3.00
2512	3.60~4.20	7.60~8.60	3.00~3.50



▪ 厚膜电阻器使用说明（Chip Resistor Instructions for use）

本产品在以下特殊环境下应用，性能可能会受到影响：
（Application of the products in a special environment can deteriorate product performance）：

1. 高温；
   High temperature
2. 有海风或腐蚀性气体，包括氯气，硫化氢，氨气，二氧化硫，二氧化氮等；
   Near the sea ,or corrosive gas, such as Cl_2,H_2S,NH_3,SO_2,and NO_2,etc;
3. 各种类型的液体，包括水，油，化学品，有机溶剂的使用；
   Unverified liquids, such as water,oil,chenical or organic solvent;
4. 在用树脂或其他涂层材料密封产品的情况下使用；
   Unverified resin or paint to cover products;
5. 焊接后使用不洁焊剂或使用水或水溶性清洁剂清洗产品
   Products should be washed with soluble cheaner even if non cleaning flux.

- 储存 / 搬运条件（Storage / Carry conditions）

1. 储存温度 25±5℃　　Temperature：25±5℃
2. 湿度 30~70%RH　　Humidity：30~70%RH
3. 储存期限：先进先出，2 年　　Storage life：2years FIFO
4. 存放和搬运时，请保持盒子的正确方向。严禁跌落在箱体上，否则可能损坏产品电极或本体
   Please hold box correct orientation when storing and carrying.It is strictly prohibited to fall on the box. otherwise the product electrode or body may be damaged.

▪ 修订履历 (Revision History)

版本 Version	修订日期 Revision Date	修订内容 Revision Description	版本确认 Version Checked
FJ-JS-3001-V1.0	2020.12.01	原版 The original version	魏效振 Xiaozhen Wei
FJ-JS-3001-V2.0	2025.09.24	版本及格式修订 Version and format revision	魏效振 Xiaozhen Wei
FJ-JS-3001-V3.0	2026.06.13	1. 上胶带剥离力由200 改为 300 2. 增加“建议焊盘尺寸”	青立旦 Lidan Qing