



EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM P SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**
Input Voltage Selection: **Dual AC (Series/Parallel)**
Filter Switch Type: **DPST**
Filter Shield Type: **Filter Shield**
Product Orientation: **Vertical**

[All CORCOM P SERIES MULTI-FUNCTION INLET FIL \(300\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	DPST
Output Termination Type	.187" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Extender Options	None
Fuse Options	Single

Electrical Characteristics

Input Voltage Selection	Dual AC (Series/Parallel)
Leakage Current (Max) (120VAC, 60Hz)	250 μ A



Leakage Current (Max) (250VAC, 50Hz)	500 µA
Current Rating	10 A
Operating Voltage	250 VAC

Body Features

Filter Shield Type	Filter Shield
Product Orientation	Vertical

Mechanical Attachment

Panel Mount Feature Type	Snap-In
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1609146-1
PA101 CONNECTOR PLU=F6998

TE Part # 1609146-2
PA102 CONNECTOR PIN=F6999

TE Part # 1609140-1
PA100=F6800

TE Part # 1609140-3
PA105 J0=F6806

Also in the Series | Corcom P

EMI & EMC Accessories(4)

Multi-Function Inlet Filters(368)

Customers Also Bought

TE Part #207516-5
HDP-20,RCPT,SIZE 3, 25 POSN,CL

TE Part #1445421-3
REC,8-4,FLNG MT,LG INS,STD KEY

TE Part #3-1462037-0
IM07TS=IM RELAY 200mW 24V

TE Part #1604196-1
NUT,JAM,5/8-24,PKG QTY 100

TE Part #1445730-1
STRN RELIEF ASY,STRT SIZE 8

TE Part #213283-2
HARDWARE KIT,DRAWER CONN

TE Part #350428-4
02P UMNL PIN HDR ASSY NATL AU

TE Part #1-87631-5
20 MODIV HSG COMP DR .100 POL

TE Part #3-6609107-2
PS0SXSS3A=C1078

TE Part #GAG15K4D489
ESAP-ESA PROBE-400601408



Documents

Product Drawings

PS0SXSSXA=C1099

English

CAD Files

Customer View Model

ENG_CVM_4-6609107-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_4-6609107-5_A.3d_stp.zip

English

Customer View Model

ENG_CVM_4-6609107-5_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-6609107-5_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-6609107-5_O.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_4-6609107-5_O.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English