



Connectors > Circular Connectors > Circular Connector Accessories > Circular Connector Keying Plugs



Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Body Features

Primary Product Color	Black
-----------------------	-------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Compatible With Connector Cavity Type	Pin Cavities
---------------------------------------	--------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM71-C83998BB
CPC SERIES 3

TE Part # CAT-AM71-C83998CC
CPC Connector Housing, Series 4

TE Part # 206508-1
TYPE XII KEYING PLUG

Also in the Series | AMP CPC

Circular Connector Adapters(7)

Circular Connector Caps & Covers(16)

Circular Connector Hardware(3)

Circular Connector Keying Plugs(2)

Circular Power Connectors(458)

Connector Backshells(56)

Connector Seals & Cavity Plugs(36)

Connector Strain Relief(6)

Insertion & Extraction Tools(1)

Power Contacts(6)

Sealing Sleeves(2)

Customers Also Bought



TE Part #8-6609107-0
PS0S0DS3B=C1264



TE Part #164163-2
PIN ASSY



TE Part #66740-2
TYPE XII FEMALE CONT (L.P.)



TE Part #654557-000
D-436-0185



TE Part #680106-000
D-609-05



TE Part #CTL-16-513
JUNCTION ASSY



TE Part #1217757-1
TERM,POKE-IN,LP, MAG-MATE



TE Part #5-146135-6
14 MODII HDR DRST SFMNT B/A



TE Part #583691-3
RETAINING SPRING PLATED

Documents

Product Drawings
PLUG, TYPE XII KEYING
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_207597-1_F.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_207597-1_F.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_207597-1_F.3d_stp.zip
English
3D PDF
English



Customer View Model

[ENG_CVM_207597-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_207597-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_207597-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[UL Report](#)

English