

2329542-4  ACTIVE

TE Internal #: 2329542-4


Interface Seal, Silicone Rubber, Blue, -30 – 105 °C [-22 – 221 °F]

Operating Temperature

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Interface Seal**

Primary Product Material: **Silicone Rubber**

Primary Product Color: **Blue**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-30 – 105 °C [-22 – 221 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Interface Seal
----------------------------	----------------

Body Features

Primary Product Material	Silicone Rubber
--------------------------	-----------------

Primary Product Color	Blue
-----------------------	------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
-----------------------------	----------------

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)
--	---

Candidate List Declared Against: JUNE
2023 (235)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #66101-3
III+ SKT,18-16,15AU/FL,LP



TE Part #172074-1
187 HSG. PLMKII REC. NAT



TE Part #170324-1
187 PL MKII REC. 24-20AWG PTBR



TE Part #7-1393114-3
KUHP-11DT1-24=KU



TE Part #1-2321928-1
TAB TER SDL2.5 WATERPROOF
LOOSE PIECE



TE Part #2321918-4
PLUG HOUSING SDL2.5
WATERPROOF 4PIN



TE Part #2321919-2
FRONT TPA PLUG HOUSING, 2 POS



TE Part #2321922-2
REAR WIRE SEAL 2PIN



Documents

Product Drawings

PERIMETER SEAL, 4P

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2329542-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2329542-4_A.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2329542-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English