



Economy Power

TE Internal #: 5-1123722-5

Housing, Plug, Wire-to-Board, 5 Position, .155 in [3.95 mm]

Centerline, Crimp, 1 Row, Black, Mating Retention, Wire & Cable,

Economy Power

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **3.95 mm [.155 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	5
Number of Rows	1

Body Features

Primary Product Color	Black
-----------------------	-------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

--	--



Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Centerline (Pitch)	3.95 mm[.155 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1318912-1
EP CONN LP REC



TE Part # 1-1123724-5
3.96EP HDR ASSY 5(9)P NATURAL



TE Part # 1744416-5
5 POS EP II HSG, GLOW WIRE



TE Part # 1123721-2
ECONOMY POWER CONN REC CONT



TE Part # 7-1123722-5
3.96 EP PLUG HSG 5P(NATURAL)



TE Part # 5-1123723-5
3.96 EP HDR ASSY 5P(BLACK)



TE Part # 1123721-1
EP CONN. REC CONTACT



TE Part # 1-1318301-5
3.96EP HDR ASSY 5(9)P NAT/TUBE



TE Part # 1-1473059-5
3.96 EP CONN. HDR ASSY 5/7P(W/O4, 6)



TE Part # 1-1565036-5
EP CONN HDR ASSY 5/8P SPECIAL



TE Part # 1744495-5
05P EP-II HOUSING, GREEN



TE Part # 2-1123724-5
3.96EP HDR ASSY 5(9)P YELLOW



TE Part # 2-1565036-5
EP CONN HDR ASSY 3.96/7.92MM P



TE Part # 3-1123724-5
3.96EP HDR ASSY 5(9)P BLUE



TE Part # 3-1565036-5
EP CONN.HDR ASSY 5/8P SPECIAL (NO.2,5,7



TE Part # 4-1123724-5
3.96EP HDR ASSY 5(9)P RED



TE Part # 4-1565036-5
EP CONN.HDR ASSY 5/8P NATURAL (NO.2,4,6



TE Part # 5-1123724-5
3.96EP HDR ASSY 5(9)P BLACK



TE Part # 5-1565036-5
EP CONN HDR ASSY 3.96/7.92MM P



TE Part # 5-1744105-4
EP HDR ASSY 5P omit 2&4,black

Also in the Series | Economy Power



Connector Contacts(1)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(162)



PCB Latches, Locks & Retainers(2)



Power Contacts(8)



Rectangular Connector Housings(1)



Rectangular Power Connectors(302)




Wire-to-Board Connector Assemblies & Housings(142)



Wire-to-Board Connector Contacts(6)

Customers Also Bought



TE Part #HPP845E031R4
I.C 21D RH/T B400



TE Part #2309409-2
DDR4 SODIMM 260P 5.2H STD




TE Part #1318912-1
EP CONN LP REC



TE Part #1123721-2
ECONOMY POWER CONN REC
CONT



TE Part #4-1123722-5
3.96 EP PLUG HSG 5P(RED)



TE Part #1-216093-4
AMP-LATCH PRE-ASSY DIL WITHO



TE Part #1565917-4
EMBOSS ASSY DDR2 SODIMM
SOCKET 200P 5.2H



TE Part #747467-1
09 APFL PLUG RA 590



Documents

Product Drawings

3.96 EP PLUG HSG 5P(BLACK)

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1123722-5_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1123722-5_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1123722-5_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773885-9 Economy Power Connectors

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_5-1123722-5_02212018922_dmtec

English

MD_5-1123722-5_02212018922_dmtec

English

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese

Economy Power (EP) Connector



Japanese

[Agency Approvals](#)

[UL Report](#)

English