




EMI & EMC Solutions > EMI Filters > Multi-Function Inlet Filters > CORCOM M SERIES MULTI-FUNCTION INLET FIL



Filter Type: **Power Entry Module**
Input Voltage Selection: **Single AC**
Filter Switch Type: **No Switch**
Filter Shield Type: **Filter Shield**
Product Orientation: **Right Angle**

[All CORCOM M Series Multi-Function Inlet Fil \(28\)](#)

Features

Product Type Features

Ground Choke Option	No
Filter Type	Power Entry Module
Filter Switch Type	No Switch
Output Termination Type	.110" FASTON
Filtering Requirements	Filtered
Filter Connector Type	IEC 320/C-14

Configuration Features

Fuse Options	Dual, Single
--------------	--------------

Electrical Characteristics

Input Voltage Selection	Single AC
Leakage Current (Max) (120VAC, 60Hz)	300 µA
Leakage Current (Max) (250VAC, 50Hz)	500 µA
Current Rating	3 A



Operating Voltage	120 VAC, 240 VAC
-------------------	------------------

Body Features

Filter Shield Type	Filter Shield
Product Orientation	Right Angle

Mechanical Attachment

Panel Mount Feature Type	Flanged
--------------------------	---------

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Other

EMI Filters Comment	Voltage Fixed
---------------------	---------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts





TE Part # CAT-C8114-M1
CORCOM M SERIES MULTI-FUNCTION INLET FIL

Also in the Series | Corcom M



EMI & EMC Accessories(2)



Multi-Function Inlet Filters(28)



Potentiometers(5)

Customers Also Bought



TE Part #CV7361-000
202K132-25L-0



TE Part #6609108-5
PE0S0DZXC M0=C7043



TE Part #100645-3
250 FASTON, FLAG, REC., 14-17AWG, PHBRZ



TE Part #60-0001-011-000
CONTACT SOCKET 1 MM




TE Part #7-2836263-7
OCEAN_2.0 MSPS_SPARE_PART_KIT-046F




TE Part #ASA046N0085050A000
617 PLUG, SPEEDTEC



TE Part #180464-4
250 FASTON, FLAG, REC., 14-17AWG, PB



TE Part #2428585-1
MATEAX90 INERF.AD.-MAN. TOOLSET



TE Part #3-2836263-2
OCEAN_2.0 MSPS_Applicator-S-046F



TE Part #7-2836900-7
OCEAN_2.0_SPARE_PART_KIT-037F



Documents

Product Drawings

3EZM1S=F8122

English

CAD Files

Customer View Model

ENG_CVM_CVM_6609132-8_C1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_6609132-8_C1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_6609132-8_C1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE

English

1654001_CORCOM_PRODUCT_GUIDE_M_SERIES

English

Corcom Combined Selector Charts

English