

641944-1

✓ ACTIVE


AMP-IN

TE Internal #: 641944-1

PCB Terminals, Receptacle, PCB Hole Diameter 1.4 – 1.55 mm [.055 – .061 in], Through Hole - Solder, Pre-Tin Plating, Reel

[View on TE.com >](#)

Terminals & Splices > PCB Terminals

PCB Terminal Type: **Receptacle**PCB Thickness (Recommended): **1.19 mm [.047 in]**PCB Hole Diameter: **1.4 – 1.55 mm [.055 – .061 in]**Mating Pin Diameter: **1.47 mm [.058 in]**Profile Height from PCB: **5.33 mm [.212 in]****Features****Product Type Features**

Terminal Features

Stud Hole

Contact Features

PCB Terminal Type

Receptacle

Mating Pin Diameter

1.47 mm[.058 in]

Terminal Plating Material

Pre-Tin

Terminal Size

Miniature

Terminal Orientation

Straight

Termination Features

Termination Method to Printed Circuit Board

Through Hole - Solder

Product Terminates To

Printed Circuit Board

Mechanical Attachment

Wire Insulation Support

Without

Dimensions

Extension Below Board

2.54 mm[.1 in]

Terminal Material Thickness	.25 mm [.01 in]
PCB Thickness (Recommended)	1.19 mm [.047 in]
PCB Hole Diameter	1.4 – 1.55 mm [.055 – .061 in]
Profile Height from PCB	5.33 mm [.212 in]

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]

Packaging Features

Packaging Quantity	10000
Packaging Method	Reel

Product Compliance


For compliance documentation, visit the product page on TE.com >

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

[.058 DIA PIN PC PTPHBZ](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_641944-1_G_c-641944-1-g.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_641944-1_G_c-641944-1-g.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_641944-1_G_c-641944-1-g.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English