



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Panel, Wire-to-Wire**
Number of Positions: **8**
Centerline (Pitch): **4.95 mm [.195 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Layout	Matrix
Contact Retention Within Housing	Without



Contact Type	Pin
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Panel Mount Feature	With
Panel Mount Feature Type	Mounting Brackets
Connector Mounting Type	Panel Mount
Housing Features	
Centerline (Pitch)	4.95 mm[.195 in]
Housing Color	Natural
Housing Material	Nylon 6/6
Dimensions	
Panel Thickness (Recommended)	25.9 – 64.51 mm[1.02 – 2.54 in]
Connector Height	23.62 mm[.93 in]
Product Width	28.45 mm[1.12 in]
Product Length	14.73 mm[.579 in]
Row-to-Row Spacing	9.14 mm[.36 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Identification Marking	
Circuit Identification Feature	Without
Industry Standards	
CSA Rating	Certified
UL Rating	Recognized
Agency/Standard	CSA, UL
Approved Standards	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire
Packaging Features	



Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 60618-5
CMNL PIN AUBR L/P



TE Part # 60618-4
CMNL PIN PTPPHBZL/P



















TE Part # 61174-1
CMNL PIN L/P PTBR







TE Part # 60620-1
CMNL PIN 20-14 TPBR L/P



 <p>TE Part # 60620-4 CMNL PIN 20-14 TPPHBZ L/P</p>	 <p>TE Part # 163305-2 MATENLOK PIN SDW</p>	 <p>TE Part # 61118-5 CMNL PIN 20-14 AUNIBR</p>	 <p>TE Part # 61116-4 CMNL PIN 24-18 PTPHBZ</p>
 <p>TE Part # 163555-6 MATENLOK PIN</p>	 <p>TE Part # 61118-4 CMNL PIN 20-14 TPPHBZ</p>	 <p>TE Part # 925075-7 4W CIRCULAR MATE-N-LOK PIN HSG NAT</p>	 <p>TE Part # 350079-1 MNL PIN 30-22 PTPBR</p>
 <p>TE Part # 163301-6 MATENLOK PIN</p>	 <p>TE Part # 163301-8 MATENLOK PIN</p>	 <p>TE Part # 61116-1 CMNL PIN 24-18 PTBR</p>	 <p>TE Part # 61527-2 CMNL GROUDING PIN 22-18 PTPBR</p>
 <p>TE Part # 163303-6 MATE-N-LOK PIN</p>	 <p>TE Part # 61118-1 MNL PIN 20-14 TPBR</p>	 <p>TE Part # 163558-2 PIN M-N-L</p>	 <p>TE Part # 60618-1 CMNL PIN PTPBR L/P</p>

Also in the Series | Commercial Pin and Socket Connectors

 <p>Connector Contacts(2)</p>	 <p>Crimp Wire Pins, Tabs & Ferrules(1)</p>	 <p>Insertion & Extraction Tools(2)</p>	 <p>Power Contacts(39)</p>
--	---	--	---



Rectangular Connector Housings(10)



Rectangular Power Connectors(84)



Standard Rectangular Connectors(1)

Customers Also Bought




TE Part #543633P064
SCT-NO.1-E6-0-STK




TE Part #3-520140-4
ULTRA-FAST 250 ASY REC 16-14 AWG
TPBR




TE Part #2-520128-2
ULTRA-FAST 250 ASY REC 22-18 AWG
TPBR



TE Part #62310-2
AMVAR SPLC 7000-13000 025TPBR



TE Part #62308-2
AMVAR SPLC 3000-7000 020TPBR



TE Part #62306-2
AMVAR SPLC 1500-5000 020TPBR



TE Part #1-480708-0
12P UMNL PLUG HSG NATL



TE Part #4-280050-1
250 FASTON,FLAG,REC.,16-20 AWG,
BR



TE Part #691499-1
SPRING-FEED FINGER



TE Part #2844801-1
DOOR LEFT, MODIFIED G II+

Documents

Product Drawings
08P CMNL CAP HSG D/L
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_794048-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_794048-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794048-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English

Agency Approvals

[Agency Approval Document](#)

English

[Agency Approval Document](#)

English