




PIDG

TE Internal #: 696451-1
Knife Disconnects, Nickel, Wire Insulation Support, 22 – 16 AWG
Wire Size, .26 – 1.65 mm² Wire Size, .51 – 3.26 kcmil Wire Size,
Loose Piece, PIDG

[View on TE.com >](#)

Terminals & Splices > Knife Disconnects



Body Plating Material: **Nickel**
Wire Insulation Support: **With**
Compatible Insulation Diameter (Max): **3.18 mm [.125 in]**
Wire Size: **.26 – 1.65 mm²**

Features

Body Features

Insulation Material	Nylon
Body Plating Material	Nickel

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter (Max)	3.18 mm[.125 in]
Wire Size	.51 – 3.26 kcmil

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Insulation Option	Partially Insulated
Operating Temperature Range	105 °C[221 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece



Other

Barrel Color	Red
--------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 354940-1 PRO-CRIMPER III FRAME W/O DIES	 TE Part # 59824-1 TETRA-CRIMP PIDG PG FASTON 22-10 ASSY	 TE Part # 47386 DAHT PG PIDG 26-16 ASSY	 TE Part # 59250 T-HEAD PIDG 26-14 ASSY
--	---	--	---



TE Part # 189721-1
HAND NON-LOGIC POWER UNIT



TE Part # 189722-1
FOOT NON-LOGIC POWER UNIT



TE Part # 58433-3
PRO CR ASSY, RBY IS9252



TE Part # 2217480-1
KIT, BTLI, SDE OPEN HEAD



TE Part # 1901260-1
CCII 16MAX ASSY



TE Part # 2217480-2
KIT, BTLI, SDE OPEN HEAD



TE Part # 2217485-1
KIT, BTLI, T-HEAD



TE Part # 2217485-2
KIT, BTLI, T-HEAD



TE Part # 59300
T-HEAD PIDG PG 26-16 ASSY



TE Part # 9-1478240-0
SDE SA PEW12 HAND TOOL FRAME- NO DIES



TE Part # 169400
CERTI-LOK FRAME W/O DIES

TE Part # 1490567-1
HAND NON-LOGIC SHORT POWER UNI

TE Part # 1673611-1
SHORT TOOL HOLDER W/RATCHET



TE Part # 1SET191001R0000
CRIMP-HT



TE Part # 1SET191002R0000
TET CRIMP-HT




TE Part # 169404
CERTI-LOK DIE

Also in the Series | PIDG



Compression Connectors(17)



Crimp Terminal Housings(1)



Crimp Wire Pins, Tabs & Ferrules(41)



Hand Crimping Tools(2)



Knife Disconnects(11)




PCB Terminals(7)



Quick Disconnects(49)



Ring Terminals(611)



Spade Terminals(233)



Special Purpose Terminals(1)



Splices(46)

Customers Also Bought



TE Part #206438-1
CPC RECPT ASSEMBLY SIZE 23-57




TE Part #66107-4
III+ PIN,26-24,30AU/FL,LP



TE Part #205842-1
CPC PLUG ASSEMBLY SIZE 23-63




TE Part #770587-1
24P MINI UMNL PLUG HSG



TE Part #2-1761607-3
IDC LOW PRO HDR 10P RA LG LAT



TE Part #768838-000
CM-SCE-TP-1/4-4H-9




TE Part #527479-000
202C621-71/86-0



TE Part #775210-000
S01-03-R



TE Part #201580-1
SKT CONT ASSY,TYPE II



TE Part #M15570-22-1
TOOL INS/REM

Documents



Product Drawings

PIDG 22-16 K-D,NI-PL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_696451-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_696451-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_696451-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

RADIATION_RESISTANT_PRE-INSULATED_TERMINALS_SPLICES

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance

English

Product Compliance

English