



MTA 156

TE Internal #: 1744001-4

Rectangular Power Connectors, Header, Plug, Wire-to-Board, 4 Position, 3.96 mm [.156 in] Centerline, Printed Circuit Board, UL 94V-0, MTA 156

[View on TE.com >](#)

Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Header Type	Partially Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	4
PCB Mount Orientation	Vertical
Number of Power Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features



Mating Post Length	10.16 mm[.4 in]
PCB Contact Termination Area Plating Material Thickness	3.81 – 8.89 µm[150 – 350 µin]
Contact Layout	Inline
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Bright
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	150 – 350 µm[3.81 – 8.89 µin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Strain Relief	Without
Mating Retention	With
Mating Alignment	Without
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Polarized Lock
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Natural
Housing Material	Polyester - GF

Dimensions

Product Width	10.79 mm[.425 in]
Product Length	15.72 mm[.619 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application



Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 <p>TE Part # 3-643819-4 04P MTA156 CONN ASSY 22AWG RED</p>	 <p>TE Part # 3-643818-4 04P MTA156 CONN ASSY 20AWG YEL</p>	 <p>TE Part # 640551-4 04P MTA156 COVER</p>	 <p>TE Part # 3-643820-4 04P MTA156 CONN ASSY 24AWG WHT</p>
 <p>TE Part # 640643-4 04P MTA156 COVER F/T</p>	 <p>TE Part # 643071-4 04P MTA156 FD-THRU COVER</p>	 <p>TE Part # 3-643821-4 04P MTA156 CONN ASSY 26AWG LF</p>	 <p>TE Part # CAT-103156-WBHSM Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156</p>
 <p>TE Part # 770598-4 04P SL156 HSG W/O LCK RAMP</p>	 <p>TE Part # 643067-4 04P MTA156 CMOLDED COVER</p>	 <p>TE Part # 3-643817-4 04P MTA156 CONN ASSY 18AWG ORA</p>	 <p>TE Part # 3-644878-4 04P MTA156 ASSY ON TAPE LF</p>
 <p>TE Part # 3-647178-7 07P MTA156 HDRASSY WO#2,4,6 LF</p>			

Also in the Series | MTA 156

 <p>Insertion & Extraction Tools(1)</p>	 <p>PCB Connector Covers(88)</p>	 <p>PCB Connector Keying(2)</p>	 <p>PCB Connector Mounting(1)</p>
--	--	--	--



PCB Headers & Receptacles(314)



Power Contacts(2)



Rectangular Power Connectors(698)



Standard Rectangular Connectors(337)



Wire-to-Board Connector Contacts(2)

Customers Also Bought



TE Part #2-34541-1
PIDG SPD 22-16 COMM 22-18MIL 6



TE Part #521368-2
ULTRA-POD 250 ASSY REC 22-18
AWG TPBR



TE Part #1-1123722-5
3.96 EP PLUG HSG 5P(NATURAL)



TE Part #1-1123722-6
3.96 EP PLUG HSG 6P(NATURAL)



TE Part #61988-2
250 FASTON REC 22-18 AWG TPBR




TE Part #794220-1
MINI UMNL2 PIN 22-18 AWG SN



TE Part #1393118-2
KUP-14A55-24=KU



TE Part #794199-1
12P MINI UMNL2 CAP HSG DBLROW



TE Part #1744001-6
06P MTA156 HDR POL .045SQ TIN

Documents



Product Drawings

04P MTA156 HDR POL .045SQ TIN

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1744001-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1744001-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1744001-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English