



Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Connector Mounting



Number of Positions: **26**

Centerline (Pitch): **2 mm [ .079 in ]**

Wire Size: **28 – 24 AWG**

Primary Product Color: **Ivory**

Operating Temperature Range: **-30 – 105 °C [ -22 – 221 °F ]**

Features

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 26 |
|---------------------|----|

Body Features

|                          |       |
|--------------------------|-------|
| Primary Product Material | PA 66 |
| Primary Product Color    | Ivory |

Housing Features

|                    |               |
|--------------------|---------------|
| Centerline (Pitch) | 2 mm[.079 in] |
|--------------------|---------------|

Dimensions

|                    |                   |
|--------------------|-------------------|
| Product Width      | 7.55 mm[.297 in]  |
| Product Length     | 30.3 mm[1.193 in] |
| Product Height     | 6.65 mm[.261 in]  |
| Row-to-Row Spacing | 6.6 mm            |
| Wire Size          | 28 – 24 AWG       |

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -30 – 105 °C[-22 – 221 °F] |
|-----------------------------|----------------------------|

Packaging Features

|                    |      |
|--------------------|------|
| Packaging Quantity | 1000 |
| Packaging Method   | Bag  |

Other



|                             |                                                                              |
|-----------------------------|------------------------------------------------------------------------------|
| Connector Accessory Comment | For Use With CT Connector, Two receptacle connectors are applied per holder. |
|-----------------------------|------------------------------------------------------------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                 |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                       |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                       |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                         |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JUNE 2023 (235)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                             |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                    |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM7017-C7671  
Common Termination Contacts — POWER TRIPLE LOCK

TE Part # CAT-3980700-DRWBSV  
CT 2mm Dbl Row Assembly w/Boss: Vert.

TE Part # 353918-1  
CT 1.5MM REC CONT CRIMP TYPE

TE Part # 2-292138-6  
CT DOUBLE ROW ASSY H 26P HDR N







TE Part # CAT-AM7017-H8172  
AMP COMMON TERMINATION HOUSINGS

Also in the Series

AMP CT



PCB Connector Mounting(46)



PCB Headers & Receptacles(756)



Wire-to-Board Connector Assemblies & Housings(256)




Wire-to-Board Connector Contacts(8)

Customers Also Bought




TE Part #1-179228-3  
CT CRIMP-2 REC HSG 13P NATURAL



TE Part #1-353908-7  
Mini Common Termination (CT) Housings




TE Part #1-292254-1  
CT RELAY HDR ASSY 11P NAT



TE Part #1-292215-1  
MINI CT SGL RELAY 11P NAT



TE Part #3-353293-9  
1.5MM CT MT REC ASSY 19P BLACK



TE Part #2-292216-2  
MINI CT D/R RELAY 22P V NAT

TE Part #9-292112-4  
MT REC ASSY (#26,28)

TE Part #9-292112-0  
MT REC ASSY (#26,28)

TE Part #8-292112-8  
MT REC ASSY (#26,28)



Documents

Product Drawings

CT DOUBLE ROW 26P HOLDER NATU.

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-175133-6\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-175133-6\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-175133-6\_E.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Crimping of AMP 2.0mm Pitch, CT Crimp Typell Rec Contact

English

Application Specification

English

Product Environmental Compliance

MD\_2-175133-6\_010520172319\_dmtec

English

MD\_2-175133-6\_010520172319\_dmtec

English

Agency Approvals

CSA Certificate

English