




TE Internal #: 1-1734598-5

PCB Mount Header, Vertical, Wire-to-Board, 15 Position, 1.25 mm [.049 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, Signal, Natural

[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles > AMP HPI 1.25 mm Headers



Connector System: **Wire-to-Board**

Number of Positions: **15**

Number of Rows: **1**

Centerline (Pitch): **1.25 mm [.049 in]**

PCB Mount Orientation: **Vertical**

[All AMP HPI 1.25 mm Headers \(100\)](#)

Features

Product Type Features

Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Header

Configuration Features

Connector Contact Load Condition	Fully Loaded
Number of Positions	15
Number of Rows	1
PCB Mount Orientation	Vertical

Electrical Characteristics

Operating Voltage	100 VAC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.08 μm[120 μin]
Contact Layout	Inline



Mating Tab Width	.76 mm[.03 in]
Mating Tab Thickness	.3 mm[.012 in]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Finish	Matte
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Tin
Contact Type	Pin
Contact Current Rating (Max)	.8 A

Termination Features

Rectangular Termination Post & Tail Thickness	.3 mm[.012 in]
Rectangular Termination Post & Tail Width	.35 mm[.014 in]
Termination Post & Tail Length	1.7 mm[.067 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	Without
PCB Mount Retention	Without

Housing Features

Housing Material	PA 9T GF
Centerline (Pitch)	1.25 mm[.049 in]

Dimensions

Connector Length	20.5 mm[.807 in]
Connector Height	4.7 mm[.185 in]
Connector Width	3.2 mm[.126 in]

Usage Conditions

Operating Temperature Range	-25 – 85 °C[-13 – 185 °F]
-----------------------------	---------------------------

Operation/Application

--



Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	30
Packaging Type	Box, Tube

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1734193-1
WTB Socket,Terminal 80u" Tin

TE Part # 1-440146-5
1.25mm WTB Socket,Housing,15p

TE Part # 440147-2
1.0 WTB Terminal 30u" Au

Customers Also Bought

TE Part #2344657-5
FPC ANTENNA, CABLE, MHF, Wi-Fi TRIPLE

TE Part #2344657-7
FPC ANTENNA, CABLE, MHF, Wi-Fi TRIPLE

TE Part #1-2319764-3
E STACK PIANO 6P G LONG TUBE PD OFF

TE Part #4-2176379-9
RQ 0805 340R 0.1% 10PPM 5K RL

TE Part #1-747947-5
KIT,RCPT,25P,HDE,SHLD ENCLSRE

TE Part #EJ1953-000
06151413

TE Part #2273076-3
M12 x 1.0 angled plug pigt A

TE Part #5-2176408-3
3560 5M6 5%

TE Part #6-103325-5
15 MODII HD SRRA B/A .100CL,LF

TE Part #AKA012N00410100000
623 EXTENSION, SPEEDTEC

Documents

Product Drawings

1.25 WTB HDR DIP, 15 POS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1734598-5_R.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-1734598-5_R.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1734598-5_R.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HPI Connectors QRG](#)

English

Product Specifications

[Application Specification](#)

English