



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Strain Relief: **Without**

Primary Product Color: **Natural**

Operating Temperature (Max): 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C [158 °F, 167 °F, 176 °F, 185 °F, 194 °F, 212 °F]

Operating Temperature Range: -40 – 100 °C [-40 – 212 °F]

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
---	-------

Body Features

Primary Product Color	Natural
-----------------------	---------

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C [158 °F][167 °F][176 °F][185 °F][194 °F][212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Other

Serviceable	Yes
-------------	-----

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-HVH5375 High-Voltage Header	 TE Part # 2103245-2 Inner Housing, Split Hdr, Key B, HVA280	 TE Part # 1-2103124-1 HEADER ASSY, Ag SHIELD, KEY A, HVA280-2P	TE Part # YHVA280-2PHX-HDR-A HVA280 2P (2103124-1) HEADER, KEY A
TE Part # YHVA280-2PHX-HDR-D HVA280 2P (2103124-4) HEADER, KEY D	TE Part # YHVA280-2PHX-HDR-E HVA280 2P (2103124-5) HEADER, KEY E		



Also in the Series | **HVA 280**

Automotive Connector Caps & Covers (5)	Automotive Connector EMC Shielding (15)	Automotive Housings(78)	Connector Seals & Cavity Plugs(8)
Electric, Hybrid & Fuel Cell Cable Assemblies(6)	High Voltage Wire Processing Equipment(7)	Other Automotive Connector Accessories(7)	PCB Headers & Receptacles(37)

Customers Also Bought

TE Part #1-1355730-1 3pos MQS .63 header 90deg	TE Part #1-2177053-3 2POS,8MM HV,PLUG HSG,ASSY, SEALED	TE Part #360051-1 CLUSTER BLOCK	TE Part #HD17-9-1939S PLUG ASM
TE Part #2103340-1 HVA280 3 Bay Header Sub-Assy, KEY A,D,E	TE Part #1-968853-3 AMP MCP 2.8, CONTACT	TE Part #1-968318-1 12POS MQS REC COD A	TE Part #2-1703930-1 NANOMQS, RECEPTACLE TERMINAL
TE Part #1-2103212-1 Plug Assembly, 350A, MSD	TE Part #1599105-1 RECEPTACLE CLUSTER PIN .090dia		



Documents

Product Drawings

SHIPPING CAP, CAP, HVA280-3PM

English

CAD Files

Customer View Model

ENG_CVM_CVM_1587733-1_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1587733-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1587733-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English