UMW IRF7469TR

40V N-Channel MOSFET

1.Features

- $V_{DS\ (V)}$=40V
- $R_{DS(ON)}$<17mΩ(V_{GS}=10V)
- $R_{DS(ON)}$<21mΩ(V_{GS}=4.5V)

2.Benefits

- Ultra-Low Gate Impedance
- Very Low $R_{DS(on)}$
- Fully Characterized Avalanche Voltage and Current


3.Applications

- High Frequency Isolated DC-DC Converters with Synchronous Rectification for Telecom and Industrial Use
- High Frequency Buck Converters for Computer Processor Power
- Lead-Free

3.Pinning information

Pin	Symbol	Description
1,2,3	S	SOURCE
4	G	GATE
5,6,7,8	D	DRAIN

SOP-8



4.Absolute Maximum Ratings T_A=25°C unless otherwise noted

Parameter		Symbol	Rating	Units
Drain- Source Voltage		V_{DS}	40	V
Gate-to-Source Voltage		V_{GS}	±20	V
Continuous Drain Current, V_{GS}=10V	T_A=25°C	I_D	9	A
Continuous Drain Current, V_{GS}=10V	T_A=70°C		7.3	A
Pulsed Drain Current ①		I_{DM}	73	A
Maximum Power Dissipation ③	T_A=25°C	P_D	2.5	W
Maximum Power Dissipation ③	T_A=70°C		1.6	W
Linear Derating Factor			0.02	mW/°C
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	°C

6.Thermal resist ance rating

Parameter	Symbol	Typ	Max	Units
Junction-to-Drain Lead	$R_{\theta JL}$		20	°C/W
Junction-to-Ambient ④	$R_{\theta JA}$		50	°C/W

Notes:

① Repetitive rating; pulse width limited by max. junction temperature.

② Starting T_J=25°C, L=8.1mH, R_G=25Ω, I_{AS}=7.2A.

③ Pulse width ≤ 400μs; duty cycle ≤ 2%.

④ When mounted on 1 inch square copper board.

7.Electrical Characteristics T_J=25°C

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	I_D=250μA, V_{GS}=0V	40			V
Breakdown Voltage Temp. Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D=1mA,Reference to 25°C		0.04		V/°C
Static Drain-to-Source On-Resistance	$R_{DS(ON)}$	V_{GS}=10V, I_D=9A ③		12	17	mΩ
		V_{GS}=4.5V, I_D=7.2A ③		15.5	21	
Gate Threshold Voltage	$V_{GS(th)}$	V_{DS}=V_{GS}, I_D=250μA	1		3	V
Drain-to-Source Leakage Current	I_{DSS}	V_{DS}=32V, V_{GS}=0V			20	μA
		V_{DS}=32V, V_{GS}=0V, T_J=125°C			100	μA
Gate-to-Source Forward Leakage	I_{GSS}	V_{GS}=16V			200	nA
Gate-to-Source Reverse Leakage		V_{GS}=-16V			-200	nA
Dynamic						
Forward Transconductance	g_{FS}	V_{DS}=20V, I_D=7.2A	17			S
Total Gate Charge	Q_g	I_D=7.2A		15	23	nC
Gate-to-Source Charge	Q_{gs}	V_{DS}=20V		7	11	nC
Gate-to-Drain ("Miller") Charge	Q_{gd}	V_{GS}=4.5V ③		5	8	nC
Output Gate Charge	Q_{oss}	V_{GS}=0V, V_{DS}=16V		16	24	nC
Turn-On Delay Time	$t_{D(on)}$	V_{DD}=20V		11		ns
Rise Time	t_r	I_D=7.2A		2.2		ns
Turn-Off Delay Time	$t_{D(off)}$	R_G=1.8Ω		14		ns
Fall Time	t_f	V_{GS}=4.5V ③		3.5		ns
Input Capacitance	C_{iss}	V_{GS}=0V		2000		pF
Output Capacitance	C_{oss}	V_{DS}=20V		480		pF
Reverse Transfer Capacitance	C_{rss}	f=1.0MHz		28		pF
Avalanche Characteristics						
Single Pulse Avalanche Energy ②	E_{AS}				210	mJ
Avalanche Current ①	I_{AR}				7.2	A

Diode Characteristics						
Continuous Source Current (Body Diode)	I_S	MOSFET symbol showing the integral reverse p-n junction diode.			2.3	A
Pulsed Source Current (Body Diode) ①	I_{SM}				73	A
Diode Forward Voltage	V_{SD}	T_J=25°C,I_S=7.2A,V_{GS}=0V ③		0.8	1.3	V
		T_J=125°C,I_S=7.2A,V_{GS}=0V ③		0.65		V
Reverse Recovery Time	t_{rr}	T_J=25°C,I_F=7.2A, V_R=15V		47	71	ns
Reverse Recovery Charge	Q_{rr}	dI/dt=100A/μs ③		91	140	nC
Reverse Recovery Time	t_{rr}	T_J=125°C, I_F=7.2A, V_R=20V		77	120	ns
Reverse Recovery Charge	Q_{rr}	dI/dt=100A/μs ③		150	230	nC

8.1Typical Characterisitics




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics




Fig 4. Nomalized On-ResistanceVs. Temperature

8.2Typical Characterisitics




Fig 5. Typical Capacitance Vs. Drain-to-Source Voltage




Fig 6. Typical Gate Charge Vs. Gate-to-Source Voltage




Fig 7. Typical Source-Drain Diode Forward Voltage




Fig 8. Maximum Safe Operating Area

8.3Typical Characterisitics




Fig 9. On-Resistance Vs. Drain Current




Fig 10. On-Resistance Vs. Drain Current




Fig 11. On-Resistance Vs. Drain Current




Fig 12. Maximum Avalanche Energy Vs. Drain Current

8.4Typical Characterisitics




Fig 13. Maximum Effective Transient Themal Impedance, Junction-to-Ambient




Fig 14a. Switching Time Test Circuit





Fig 14b. Switching Time Waveforms







Fig 15a&b. Basic Gate Charge Test Circuit and Waveform







Fig 16a&b. Unclamped Inductive Test circuitand Waveforms

9.SOP-8 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	A3	b	c	D	E	E1	e	h	L
Min	-	0.05	1.30	0.60	0.39	0.20	4.70	5.80	3.80	1.24	0.30	0.50
Max	1.75	0.20	1.50	0.70	0.47	0.24	5.10	6.20	4.00	1.30	0.50	0.80

Symbol	L1	θ
Min	1.00	0°
Max	1.10	8°

10.Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW IRF7469TR	SOP-8	3000	Tape and reel

11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.