



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >

Receptacle and Tab Housing: 16 mm Pitch, 630V



Connector Product Type:

Housing

Connector & Housing Type:

Housing for Female Terminals

Number of Positions:

4

Centerline (Pitch):

10.16 mm [ .4 in ]

Termination Method to Wire & Cable:

Crimp

All Receptacle and Tab Housing: 16 mm Pitch, 630V (4)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Housing for Female Terminals
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Retention	With
Connector Mounting Type	Panel Mount

Housing Features



Centerline (Pitch)	10.16 mm[.4 in]
--------------------	-----------------

Dimensions

Row-to-Row Spacing	16 mm[.629 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2134061-1  
DYNAMIC D7300 PIN HSG ASSY RVS  
4P XX

TE Part # 1-2069312-1  
D-7 DYNA-CLAMP D-7300 TAB 4P KIT  
M XX

TE Part # 2-2069312-1  
D-7 DYNA-CLAMP D-7300 TAB 4P KIT  
S XX

Also in the Series

Dynamic 7000 Series

PCB Headers & Receptacles(1)

Wire-to-Board Connector Assemblies  
& Housings(8)

Wire-to-Board Connector Contacts(10)

Customers Also Bought

TE Part #1-917809-2  
Receptacle and Tab Housing: 5.08 or  
10.16 mm pitch, 250-600V

TE Part #353718-2  
Contact: Component To Wire; 15A, 28-  
14 wire size

TE Part #1-179552-3  
DYNAMIC D-3200 WTW TAB HSG 3P

TE Part #316040-6  
Contact: Component To Wire ; 20-  
45A , 20-8 wire size

TE Part #1827588-2  
DYNAMIC D1000 REC CONT L AU 0.38  
um L/P

Documents

Product Drawings

DYNAMIC D7300 SOCKET HSG ASSY RVS 4P XX

Japanese

CAD Files

3D PDF

3D



Customer View Model

[ENG\\_CVM\\_CVM\\_2134059-1\\_C\\_c-2134059-1-c.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2134059-1\\_C\\_c-2134059-1-c.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2134059-1\\_C\\_c-2134059-1-c.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1-1773721-5\\_DYNAMIC\\_SERIES\\_QRG](#)

English

[1-1773732-4\\_DYNAMIC\\_SERIES\\_CATALOG\\_ENGLISH](#)

Japanese

[1-1773732-4\\_DYNAMIC\\_SERIES\\_CATALOG\\_ENGLISH](#)

English

Product Specifications

[Application Specification](#)

Japanese

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[TUV Certificate](#)

English