




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.31 – 2.08 mm²**

Terminal Orientation: **Straight**

Contact Base Material: **Brass**

Features

Configuration Features

Connection Capacity	Single
Compatible With Wire & Cable Type	Discrete Wire

Contact Features

Quick Disconnect Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Terminal Material Thickness	.51 mm[.02 in]
-----------------------------	----------------

Product Length	17.65 mm[.695 in]
Wire Size	1.31 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Agency/Standard	UL
-----------------	----

Packaging Features

Packaging Quantity	10000
Packaging Method	Strip/Reel

Other

Terminals & Splices Comment	For automotive fuse.
-----------------------------	----------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

















EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer











This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 <p>TE Part # 1438246-1 SPLICE, BUTT, HEATER WIRE 18-16 AWG BR</p>	 <p>TE Part # 61248-1 TAB INSULATION PIERCING 20-18 AWG TPCUBR</p>	 <p>TE Part # 1438246-2 SPLICE, BUTT, HEATER WIRE 18-16AWG PTPBR</p>	 <p>TE Part # 63271-1 COIL TERMINAL TERMINAL 24-20 AWG PTPBR</p>
 <p>TE Part # 962907-2 FLACHSTECK 4,8 SPEZ</p>	 <p>TE Part # 1217440-8 STRAIN RELIEF,SPECIAL PH BRZ</p>	 <p>TE Part # 1217881-1 250 FUSE RCPT 020PTPBR</p>	 <p>TE Part # 2-2150671-1 OC-PA-E-FM-140F-001-0188</p>
 <p>TE Part # 2-2150671-2 OC-PA-E-FA-140F-001-0188</p>	 <p>TE Part # 2150671-1 OC-AT-E-FM-140F-001-0188</p>	 <p>TE Part # 2150671-2 OC-AT-E-FA-140F-001-0188</p>	 <p>TE Part # 61280-1 BUTTON CONTACT 20-16 AWG BR</p>
 <p>TE Part # 61684-3 SPECIAL TAB TAB TNSL WIRE GPBR</p>	 <p>TE Part # 61684-5 SPECIAL TAB TAB TNSL WIRE NTPBR</p>	 <p>TE Part # 63723-2 RCPT TWISTLOK 20-16 0255 TPPHBZ</p>	 <p>TE Part # 7-2150671-7 OC-140F-CRIMPTOOLINGKIT</p>

Customers Also Bought

 <p>TE Part #DT04-4P REC, 4P, GRY, N</p>	 <p>TE Part #DT06-3S PLG, 3P, GRY, N</p>	 <p>TE Part #2-34123-1 TERMINAL, SOLIS R 16-14 10</p>	 <p>TE Part #58336-1 HEAD (IDC) MODU MTE W/O TL</p>
 <p>TE Part #1-480304-0 03P CMNL PLUG HSG P/M NATL</p>	 <p>TE Part #34119 TERMINAL, SOLIS R 16-14 4</p>	 <p>TE Part #1776544-6 6P .563" DR, 600V</p>	 <p>TE Part #58338-1 MTA 50/100/156 PNEUMATIC BENCH MOUNT</p>
 <p>TE Part #NB14124001 VERSAFIT-1/2-0-FSP</p>	 <p>TE Part #2-22285-6 SPRING, EXTENSION</p>		

Documents

Product Drawings

FUSE TERMINAL RECEPTACLE 16-14 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_40626_AG_c-40626-ag.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_40626_AG_c-40626-ag.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_40626_AG_c-40626-ag.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English