



Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Connector Hardware Type: **Strain Relief Clamp**

Number of Positions: **14**

Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**

Features

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 14 |
|---------------------|----|

Body Features

|                                  |                      |
|----------------------------------|----------------------|
| Strain Relief Type               | Shield & Cable Clamp |
| Primary Product Plating Material | Nickel               |
| Primary Product Material         | Carbon Steel         |
| Cable Exit Angle                 | 180°, 90°            |

Mechanical Attachment

|                         |                                               |
|-------------------------|-----------------------------------------------|
| Strain Relief           | With                                          |
| Mounting Hardware       | U Bolt, Wire Guide, Protection Sleeve and Nut |
| Thread Size             | 4-40                                          |
| Connector Hardware Type | Strain Relief Clamp                           |

Dimensions

|                |                    |
|----------------|--------------------|
| Product Width  | 15.88 mm[.625 in]  |
| Product Length | 28.58 mm[1.125 in] |
| Product Height | 31.75 mm[1.25 in]  |



Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 150 °C[-67 – 302 °F] |
|-----------------------------|----------------------------|

Packaging Features

|                    |     |
|--------------------|-----|
| Packaging Quantity | 1   |
| Packaging Method   | Bag |

Other

|                             |                                |
|-----------------------------|--------------------------------|
| Connector Accessory Comment | Hardware supplied unassembled. |
|-----------------------------|--------------------------------|

Product Compliance

For compliance documentation, visit the product page on TE.com>


|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2023 (235)<br>Candidate List Declared Against: JAN 2021 (211)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                           |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 201355-1  
MALE BLOCK 14 PL

Also in the Series | AMP M Series



Board-to-Board Jumpers & Shunts(7)




Rack & Panel Connectors(1)



Rectangular Connector Hardware(51)



Rectangular Power Connectors(66)



Standard Edge Connectors(2)

Customers Also Bought




TE Part #DTP06-2S-E004  
PLG, 2P, BLK, N



TE Part #1SET411010R0000  
WD-1-DP-GR2560



TE Part #HDP26-24-47SE-L017  
PLG, 47P, BLK, E, RNG, 16/20, S




TE Part #218204-001  
22759/34-20-9



TE Part #702841-000  
55A1821-22-9/96-9CS2275



TE Part #253789-000  
55A1831-22-MST3-9CS2275




TE Part #218203-002  
22759/34-22-9



TE Part #323763-000  
55A1821-24-9/96-9CS2275





Documents

Product Drawings

14 PL. STRAIN RELIEF CLAMP

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_200686-1\_L.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_200686-1\_L.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_200686-1\_L.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M\_SERIES\_PIN\_AND\_SOCKET\_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

Japanese

Instruction Sheet (U.S.)

English

AMP Strain Relief Clamp for 14, 20, & 26 Position Series "M" Connector

English

Agency Approvals

Agency Approval Document

English