


2-179228-4  ACTIVE

AMP CT

TE Internal #: 2-179228-4

Housing, Receptacle, Wire-to-Wire / Wire-to-Board, 4 Position, .079 in [2 mm] Centerline, Crimp, 1 Row, Blue, Wire & Cable, Power & Signal, AMP CT

[View on TE.com >](#)[Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings >](#)[AMP COMMON TERMINATION HOUSINGS](#)Connector Product Type: **Housing**Connector & Housing Type: **Receptacle**Connector System: **Wire-to-Board, Wire-to-Wire**Number of Positions: **4**Centerline (Pitch): **2 mm [.079 in]**[All AMP COMMON TERMINATION HOUSINGS \(176\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	2000 VAC
Insulation Resistance	1000 MΩ
Operating Voltage	125 VAC

Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Contact Layout	Inline
----------------	--------

Contact Type	Socket
Contact Current Rating (Max)	4 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	2 mm[.079 in]

Dimensions

Connector Length	10 mm[.393 in]
Connector Height	6.6 mm[.26 in]
Connector Width	4.6 mm[.181 in]
Wire Size	30 – 22 AWG

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard	CSA, UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	4000
Packaging Method	Bag & Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


			
TE Part # 2-292132-4 CT P/HDR BOX V 4P BLUE	TE Part # 2-292173-4 CT BOX HDR H SMT 4P O/TAPE BLA	TE Part # 2-292161-4 CT P/HDR ASSY V 4P W/KINK BLUE	TE Part # 2-292174-4 CT BOX HDR V SMT 4P O/TAPE BLA
			
TE Part # CAT-3980407-RHDRRA CT 2mm Header Assembly: Right Angle	TE Part # 2-292156-4 CT RELAY HDR ASSY FREE HANGING	TE Part # 2-292254-4 CT RELAY HDR ASSY 4P BLUE	TE Part # 2-292157-4 CT RELAY W/COMMONING BAR 4P NA



Also in the Series | AMP CT



Customers Also Bought



Documents

Product Drawings

CT CRIMP-2 REC HSG 4P BLUE

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2-179228-4_N1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-179228-4_N1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-179228-4_N1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of AMP 2.0mm Pitch, CT Crimp Typell Rec Contact

English

Application Specification

English

Product Environmental Compliance

[MD_2-179228-4_0807201798_dmtec](#)

English

[MD_2-179228-4_0807201798_dmtec](#)

English

Agency Approvals

CSA Certificate

English