WMB040N03LG2

30V N-Channel Enhancement Mode Power MOSFET

Description

WMB040N03LG2 uses Wayon's 2nd generation power trench MOSFET technology that has been especially tailored to minimize the on-state resistance and yet maintain superior switching performance. This device is well suited for high efficiency fast switching applications.



PDFN5060-8L

Features

- V_{DS} = 30V, I_D = 58A
  $R_{DS(on)}$ < 4.0mΩ @ V_{GS} = 10V
  $R_{DS(on)}$ < 6.2mΩ @ V_{GS} = 4.5V
- Low R_{DS}(on)
- Low Gate Charge
- 100% EAS Guaranteed
- RoHS and Halogen-Free Compliant

RoHS compliant



Applications

- Power Management in Switches
- DC/DC Converter

Absolute Maximum Ratings (T_A = 25°C, unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	±20	V
Continuous Drain Current	T_C=25°C	I_D	58	A
	T_C=100°C		38	
Pulsed Drain Current[1]		I_{DM}	232	A
Single Pulse Avalanche Energy[2]		EAS	88	mJ
Total Power Dissipation	T_C=25°C	P_D	28	W
Operating Junction and Storage Temperature Range		T_J , T_{STG}	-55 to 150	°C

Thermal Characteristics

Parameter	Symbol	Value	Unit
Thermal Resistance from Junction-to-Ambient[3]	$R_{\theta JA}$	51	°C/W
Thermal Resistance from Junction-to-Case	$R_{\theta JC}$	4.5	°C/W

Electrical Characteristics (T_J = 25°C, unless otherwise noted)

Parameter		Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Static Characteristics							
Drain-Source Breakdown Voltage		$V_{(BR)DSS}$	V_{GS} = 0V, I_D = 250μA	30	-	-	V
Gate-body Leakage Current		I_{GSS}	V_{DS} = 0V, V_{GS} = ±20V	-	-	±100	nA
Zero Gate Voltage Drain Current	T_J=25°C	I_{DSS}	V_{DS} = 30V, V_{GS} = 0V	-	-	1	μA
	T_J=100°C			-	-	100	
Gate-Threshold Voltage		$V_{GS(th)}$	V_{DS} = V_{GS}, I_D = 250μA	1.2	-	2.2	V
Drain-Source On-Resistance[4]		$R_{DS(on)}$	V_{GS} = 10V, I_D = 20A	-	3.6	4.0	mΩ
			V_{GS} = 4.5V, I_D = 15A	-	5.0	6.2	
Forward Transconductance[4]		g_{fs}	V_{DS} = 5V, I_D = 20A	-	76	-	S
Dynamic Characteristics[5]							
Input Capacitance		C_{iss}	V_{DS} = 15V, V_{GS} = 0V, f = 1MHz	-	1390	-	pF
Output Capacitance		C_{oss}		-	680	-	
Reverse Transfer Capacitance		C_{rss}		-	53	-	
Gate Resistance		R_G	f = 1MHz	-	2	-	Ω
Switching Characteristics[5]							
Total Gate Charge		Q_g	V_{GS} = 4.5V, V_{DS} = 15V, I_D = 20A	-	15	-	nC
Gate-Source Charge		Q_{gs}		-	5.9	-	
Gate-Drain Charge		Q_{gd}		-	3.5	-	
Turn-on Delay Time		$t_{d(on)}$	V_{GS} = 10V, V_{DD} = 15V, R_G = 3Ω, I_D = 20A	-	7.7	-	ns
Rise Time		t_r		-	20.5	-	
Turn-off Delay Time		$t_{d(off)}$		-	21.8	-	
Fall Time		t_f		-	4.5	-	
Drain-Source Body Diode Characteristics							
Diode Forward Voltage[4]		V_{SD}	I_S = 1A, V_{GS} = 0V	-	-	1.0	V
Continuous Source Current	T_C=25°C	I_S	-	-	-	58	A

Notes:

1. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}$=150°C.
2. The test condition is V_{DD}=25V, V_{GS}=10V, L=0.4mH, I_{AS}=20A.
3. The data tested by surface mounted on a 1 inch2 FR-4 board with 2OZ copper, The value in any given application depends on the user's specific board design.
4. The data tested by pulsed, pulse width ≤ 300us, duty cycle ≤ 2%.
5. This value is guaranteed by design hence it is not included in the production test.

Typical Characteristics



Figure 1. Output Characteristics



Figure 2. Transfer Characteristics



Figure 3. Forward Characteristics of Reverse



Figure 4. $R_{DS(ON)}$ vs. V_{GS}



Figure 5. $R_{DS(ON)}$ vs. I_D



Figure 6. Normalized $R_{DS(on)}$ vs. Temperature



Figure 7. Capacitance Characteristics



Figure 8. Gate Charge Characteristics



Figure 9. Power Dissipation



Figure10. Safe Operating Area



Figure 11. Normalized Maximum Transient Thermal Impedance

Test Circuit



Figure A. Gate Charge Test Circuit & Waveforms



Figure B. Switching Test Circuit & Waveforms



Figure C. Unclamped Inductive Switching Circuit & Waveforms

Mechanical Dimensions for PDFN5060-8L



COMMON DIMENSIONS

SYMBOL	MM	
	MIN	MAX
A	0.90	1.20
A3	0.15	0.35
D	4.80	5.40
E	5.90	6.35
D1	3.61	4.31
E1	3.30	3.92
E2	5.50	6.06
k	1.10	-
b	0.30	0.51
e	1.27BSC	
L	0.38	0.71
L1	0.05	0.36
H	0.38	0.71
θ	0°	12°

Ordering Information

Part	Package	Marking	Packing method
WMB040N03LG2	PDFN5060-8L	B040N03L	Tape and Reel

Marking Information



B040N03L = Device code

WWXX XXX= Date code

Contact Information

No.1001, Shiwan(7) Road, Pudong District, Shanghai, P.R.China.201207
Tel: 86-21-50310888 Fax: 86-21-50757680 Email: market@way-on.com
WAYON website: **http://www.way-on.com**
For additional information, please contact your local Sales Representative.

WAYON ® is registered trademarks of Wayon Corporation.

Disclaimer

WAYON reserves the right to make changes without further notice to any Products herein to improve reliability, function, or design. The Products are not designed for use in hostile environments, including, without limitation, aircraft, nuclear power generation, medical appliances, and devices or systems in which malfunction of any Product can reasonably be expected to result in a personal injury. The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. WAYON does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.