

product type designation



Antenna ANT793-8DK

ANT793-8DK IWLAN antenna vertically-horizontally polarized with strong directional effect incl. 2x N-female socket; 23 dBi; IP67 (-45-+70 °C), 5 GHz; Wi-Fi compliance and Observe national approvals; Mounting on wall or mast; compact instructions as hard copy German/English; scope of delivery: 1x ANT793-8DK, 1x mounting aid for alignment .

radio frequencies	
type of wireless network / is supported	WLAN
operating frequency	5.15 ... 5.875 GHz
<ul style="list-style-type: none"> for WLAN in 5 GHz frequency band 1 	
antenna gain compared to spherical radiator	23 dB
<ul style="list-style-type: none"> of the WLAN antenna / in the 5 GHz frequency band 	
electrical data	
impedance	50 Ω
polarization	Dual linear vertical-horizontal
radiation characteristic	directional
antenna gain compared to spherical radiator	23 dB
<ul style="list-style-type: none"> of the WLAN antenna / in the 5 GHz frequency band 	
standing wave ratio (VSWR) / maximum	1.7
radiating angle of the antenna	
<ul style="list-style-type: none"> in the 5 GHz frequency band / horizontal 	9°
<ul style="list-style-type: none"> in the 5 GHz frequency band / vertical 	9°
number of electrical connections / of the antenna	2
type of electrical connection / of the antenna	N-Connector
design of plug-in connection	female
angle of inclination / downward / maximum	0°
crosstalk attenuation / between the antenna connections	40 dB
front-to-back ratio	35 dB
mechanical data	
material	
<ul style="list-style-type: none"> of outer shell 	Polycarbonate
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation 	-45 ... +70 °C
<ul style="list-style-type: none"> during storage 	-45 ... +70 °C
<ul style="list-style-type: none"> during transport 	-45 ... +70 °C
protection class IP	IP67
wind load / maximum	389 N; frontal at 220 km/h
design, dimensions and weights	
width	371 mm
height	371 mm
depth	40 mm
net weight	2500 g
fastening method	

- mast mounting
- wall mounting
- roof mounting
- directly on the device

Yes
Yes
No
No

standards, specifications, approvals

certificate of suitability

- RoHS conformity

Yes

wireless approval

Current national approvals can be found on the Internet under www.siemens.com/funkzulassungen

reference code

- according to IEC 81346-2
- according to IEC 81346-2:2019

TF

TFB

further information / internet-Links

Internet-Link

- to web page: selection aid TIA Selection Tool
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

11/3/2021 