

ATGBICS TRX100090/TC Transmode Compatible Transceiver

DWDM XFP 10GBase OC-192/STM-64/10G SONET ZR Tunable (SMF, 80km, DOM)

Brand : ATGBICS

Product code: TRX100090/TC-C




Product name : TRX100090/TC Transmode Compatible Transceiver DWDM XFP 10GBase OC-192/STM-64/10G SONET ZR Tunable (SMF, 80km, DOM)

TRX100090/TC Transmode Compatible Transceiver DWDM XFP 10GBase OC-192/STM-64/10G SONET ZR Tunable (SMF, 80km, DOM)

ATGBICS TRX100090/TC Transmode Compatible Transceiver DWDM XFP 10GBase OC-192/STM-64/10G SONET ZR Tunable (SMF, 80km, DOM). SFP transceiver type: Fiber optic, Maximum data transfer rate: 10000 Mbit/s, Interface type: XFP. Product colour: Silver, Housing material: Metal, Country of origin: China. Input voltage: 3.3 V, Maximum voltage: 3.5 V, Power consumption (typical): 1 W. Number of products included: 1 pc(s), Package type: Box



Performance		Features	
SFP transceiver type *	Fiber optic	Brand compatibility	Transmode
Maximum data transfer rate *	10000 Mbit/s	Certification	CE, FCC, RoHS
Interface type *	XFP	Power	
Single-mode fiber (SMF) supported	✓	Input voltage	3.3 V
Multi-mode fiber (MMF) supported	✗	Maximum voltage	3.5 V
Fiber optic connector	LC	Power consumption (typical)	1 W
Maximum transfer distance	80000 m	Operational conditions	
Ethernet LAN	✓	Maximum operating temperature	70 °C
Ethernet interface type	10 Gigabit Ethernet	Operating temperature (T-T)	0 - 70 °C
Digital Diagnostics Monitoring (DDM)	✓	Storage temperature (T-T)	-40 - 85 °C
Features		Operating relative humidity (H-H)	0 - 95%
Product colour	Silver	Storage relative humidity (H-H)	0 - 95%
Housing material	Metal	Packaging data	
Plug and Play	✓	Number of products included	1 pc(s)
Hot-Plug support	✓	Package type	Box
Hot-swap	✓	Technical details	
Easy to install	✓	Sustainability compliance	✓
Country of origin	China	Sustainability certificates	RoHS
		Doesn't contain	Lead



5056468746511

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.