

0295	0292	0294	0398
0295-0-15-XX-06-XX-10-0 Solder mount in .063 min. mounting hole	0292-0-15-XX-06-XX-10-0 Solder mount in .071 min. mounting hole	0294-0-15-XX-06-XX-10-0 Solder mount in .076 min. mounting hole	0398-0-15-XX-06-XX-04-0 Press-fit in .066 mounting hole

0397	0297
0397-X-15-XX-06-XX-04-0 Press-fit in .066 mounting hole	0297-0-15-XX-06-XX-04-0 Press-fit in .067 mounting hole

Basic Part Number	Length V
0397-0	.353
0397-1	.333
0397-2	.413

9019/9039							
	<table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="padding: 5px;">Basic Part Number</th> <th style="padding: 5px;">Head Dia. C</th> </tr> </thead> <tbody> <tr> <td style="padding: 5px;">9019-0</td> <td style="padding: 5px;">.125</td> </tr> <tr> <td style="padding: 5px;">9039-0</td> <td style="padding: 5px;">.100</td> </tr> </tbody> </table>	Basic Part Number	Head Dia. C	9019-0	.125	9039-0	.100
Basic Part Number	Head Dia. C						
9019-0	.125						
9039-0	.100						
90X9-X-15-XX-06-XX-10-0 Press-fit in .075 mounting hole							

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°</p>	<p>ORDER CODE: <u>XXXX</u> - X - 1X - <u>XX</u> - <u>06</u> - <u>XX</u> - <u>XX</u> - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH: →</p> <p>01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL</p> <p style="text-align: center;">↑</p> <p style="text-align: center;">CONTACT</p> <p style="text-align: center;">#06 CONTACT (DATA ON PAGE 210)</p> <p>SPECIFY CONTACT FINISH: →</p> <p>01 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL</p>
--	---