




Connectors > Connector Accessories > Connector Strain Relief



Strain Relief Accessory Type: **Cable Gland**

Sealable: **Yes**

Features

Product Type Features

Strain Relief Accessory Type	Cable Gland
Sealable	Yes

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (1.9% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T2020002008-000
CDF-0.75

TE Part # T3165400111-000
BLIND-40-M

TE Part # T3161400050-000
LN-40-M

Customers Also Bought

TE Part #2-178129-6
6-P DYNAMIC PLUG-H D3200 5.08

TE Part #1-1318115-9
DYNAMIC D-2100 TAB HSG 20P F/H

TE Part #175286-5
DYNAMIC D-3 TAB CONT. L PRE-TIN

TE Part #1903114-2
Contact: Component To Wire; 3-5A, 30-18 Wire Size

TE Part #T2030001025-000
CEM-2.5

TE Part #T2040244201-000
HE-024-FC

TE Part #1-917659-5
DYNAMIC 3200 D/ROW REC HSG 10P

TE Part #1747418-2
DYNAMIC D4200 REC CONT M

Documents

Product Drawings
DLX-40-MT

English

CAD Files



3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T3609400112-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T3609400112-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T3609400112-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

HEAVY DUTY CONNECTORS

English

Product Specifications

Application Specification

English