



Figure similar

MLFB-Ordering data

6SL3220-3YH48-0UB0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		General tech. specifications	
Input			
Number of phases	3 AC		
Line voltage	500 ... 690 V +10 % -20 %		
Line frequency	47 ... 63 Hz		
Rated voltage	690V IEC	600V NEC	
Rated current (LO)	141.00 A	138.00 A	
Rated current (HO)	122.00 A	131.60 A	
Output			
Number of phases	3 AC		
Rated voltage	690V IEC	600V NEC	
Rated power (LO)	132.00 kW	150.00 hp	
Rated power (HO)	110.00 kW	125.00 hp	
Rated current (LO)	144.00 A	144.00 A	
Rated current (HO)	125.00 A	125.00 A	
Rated current (IN)	148.00 A		
Max. output current	195.00 A		
Pulse frequency	2 kHz		
Output frequency for vector control	0 ... 200 Hz		
Output frequency for V/f control	0 ... 550 Hz		
Power factor λ			
0.90 ... 0.95			
Offset factor $\cos \phi$			
0.99			
Efficiency η			
0.98			
Sound pressure level (1m)			
72 dB			
Power loss			
2.510 kW			
Filter class (integrated)			
Unfiltered			
EMC category (with accessories)			
without			
Ambient conditions			
Standard board coating type			
Class 3C2, according to IEC 60721-3-3: 2002			
Cooling			
Air cooling using an integrated fan			
Cooling air requirement			
0.153 m ³ /s (5.403 ft ³ /s)			
Installation altitude			
1000 m (3280.84 ft)			
Ambient temperature			
Operation			
-20 ... 45 °C (-4 ... 113 °F)			
Transport			
-40 ... 70 °C (-40 ... 158 °F)			
Storage			
-25 ... 55 °C (-13 ... 131 °F)			
Relative humidity			
Max. operation			
95 % At 40 °C (104 °F), condensation and icing not permissible			

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



Figure similar

MLFB-Ordering data

6SL3220-3YH48-0UB0

Mechanical data

Degree of protection	IP20 / UL open type
Size	FSF
Net weight	66 kg (146.61 lb)
Width	305 mm (12.01 in)
Height	709 mm (27.91 in)
Depth	369 mm (14.53 in)

Inputs / outputs

Standard digital inputs

Number	6
Switching level: 0→1	11 V
Switching level: 1→0	5 V
Max. inrush current	15 mA

Fail-safe digital inputs

Number	1
--------	---

Digital outputs

Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0

Analog / digital inputs

Number	2 (Differential input)
Resolution	10 bit

Switching threshold as digital input

0→1	4 V
1→0	1.6 V

Analog outputs

Number	1 (Non-isolated output)
--------	-------------------------

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy ±5 °C

Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	Yes
Torque control, with encoder	No

Communication

Communication	USS, Modbus RTU, BACnet MS/TP
---------------	-------------------------------

Connections

Signal cable

Conductor cross-section	0.15 ... 1.50 mm ² (AWG 24 ... AWG 16)
-------------------------	--

Line side

Version	M10 screw
Conductor cross-section	35.00 ... 120.00 mm ² (AWG 1 ... AWG 4/0)

Motor end

Version	M10 screw
Conductor cross-section	35.00 ... 120.00 mm ² (AWG 1 ... AWG 4/0)

DC link (for braking resistor)

PE connection	M10 screw
---------------	-----------

Max. motor cable length

Shielded	300 m (984.25 ft)
Unshielded	450 m (1476.38 ft)




Figure similar

MLFB-Ordering data

6SL3220-3YH48-0UB0

Converter losses to EN 50598-2*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-37.50 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

CE marking

EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

Operator panel: Intelligent Operator Panel (IOP-2)

Screen

Display design	LCD colors
Screen resolution	320 x 240 Pixel

Mechanical data

Degree of protection	IP55 / UL type 12
Net weight	0.13 kg (0.30 lb)
Width	70.0 mm (2.76 in)
Height	106.85 mm (4.21 in)
Depth	19.65 mm (0.77 in)

Ambient conditions

Ambient temperature during

Operation	0 ... 50 °C (32 ... 122 °F)
	55 °C only with door mounting kit
Storage	-40 ... 70 °C (-40 ... 158 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity at 25°C during

Max. operation	95 %
-----------------------	------

Approvals

Certificate of suitability CE, cULus, EAC, KCC, RCM