




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **18**

Centerline (Pitch): **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	18
Number of Rows	2

Electrical Characteristics

Termination Resistance	12 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	750 V
Operating Voltage	300 VAC

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	3 A

Termination Features



Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention	Without

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Thermoplastic
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Connector Length	22.8 mm
Connector Height	5.02 mm
Wire Size	.03 – .5 mm ²
Row-to-Row Spacing	2.54 mm[.1 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

Approved Standards	CSA LR7189, UL E28476
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-104479-0 SHORT POINT CONT 30 DPLX STMPD LF	 TE Part # 104479-9 SHORT POINT CONT 15 DPLX STMPD LF	 TE Part # 1-104480-7 SHORT POINT CONT PLTD SN	 TE Part # 104480-4 SHORT POINT CONT 30 DPLX STMPD
 TE Part # 1-104480-3 SHORT POINT CONT 30 DPLX STMPD LF	 TE Part # 104479-8 SHORT POINT CONT PLTD SN	 TE Part # 1-104480-2 SHORT POINT CONT 15 DPLX STMPD LF	 TE Part # 104480-2 SHORT POINT CONT PLTD SN-PB



TE Part # 1-104481-1
SHORT POINT CONT 30 DPLX
STMPD LF

TE Part # 1-104481-0
SHORT POINT CONT 15 DPLX
STMPD LF

TE Part # 104479-2
SHORT POINT CONT PLTD SN-PB
STMPD LF

Also in the Series | AMPMODU IV/V

Automotive Housings(2)

Backplane Connector Housings(1)

Board-to-Board Connector Contacts(6)

Connector Strain Relief(3)

Insertion & Extraction Tools(4)

PCB Connector Covers(18)

PCB Connector Keying(6)

PCB Connector Mounting(1)

PCB Headers & Receptacles(934)

PCB Latches, Locks & Retainers(7)

Rectangular Connector Housings(5)

Standard Rectangular Connectors(8)

Wire-to-Board Connector Assemblies
& Housings(447)

Wire-to-Board Connector Contacts
(322)


Customers Also Bought




TE Part #320665
PG SPD 22-16 COMM 22-18 MIL 6




TE Part #322994
TERMINAL,PG SPD 16-14 6




TE Part #1586000-4
4P FH PLUG VAL-U-LOK V2




TE Part #3-520125-2
ULTRAFAST 187 ASSY REC 16-14 TPBR LP



TE Part #1586106-3
3P RCPT VAL-U-LOK SR V0



TE Part #1586314-1
VAL-U-LOK PIN BR TN 22-18 LP




TE Part #1586317-1
VAL-U-LOK SKT BR SN 26-22 LP



TE Part #1658620-7
30 NOVO MIL 15DP, LEAD FREE



TE Part #176300-1
UNVI POWER CAP HSG 15P PNL MTG



TE Part #1586343-1
VAL-U-LOK EXTRACTION TOOL

Documents

Product Drawings

18 SHORT PT RCPT HSG DR .100CL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_104483-2_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_104483-2_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_104483-2_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

Product Specifications

Application Specification

English

Agency Approvals

UL

English