



Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Connector Assembly**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Panel**

Number of Positions: **4**

Centerline (Pitch): **250 mm [ 9.84 in ]**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Rectangular Power Connector Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Panel
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	2

Body Features

Cable Exit Angle	180°
Connector Profile	Standard

Contact Features

Contact Retention Within Housing	With
----------------------------------	------



Contact Type	Socket
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Mating Alignment Type	Blindmate
Mating Alignment	With
Panel Mount Feature	With
Panel Mount Feature Type	Screw Mount
Connector Mounting Type	Panel Mount
Housing Features	
Centerline (Pitch)	250 mm[9.84 in]
Housing Color	Black
Housing Material	Polyester GF
Dimensions	
Panel Thickness (Recommended)	1.5 – 1.78 mm[.59 – .7 in]
Connector Height	42 mm[1.654 in]
Product Width	38.75 mm[1.526 in]
Product Length	60 mm[2.362 in]
Row-to-Row Spacing	21 mm[.827 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Operation/Application	
Shielded	No
Circuit Application	Power
Identification Marking	
Circuit Identification Feature	Without
Industry Standards	
UL Rating	Certified
Approved Standards	UL 1977
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire



Packaging Features

Packaging Method	Box
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 2212243-1  
FORGE, ASSY PIN, 0#0-4#4-0#8-0#12-0#22

Customers Also Bought







TE Part #5745355-4  
50 PLUG RA/MS STD




TE Part #487526-4  
005 HOUSING FFC RCPT 100CL SR




TE Part #NB-PTCO-002  
Pt100, 2.0x2.3, Class B, PTFC101B1G0




TE Part #2-487406-2  
FFC,RCPT CONTACT,STD PRESSURE




TE Part #2176230-3  
SMD Power Resistor: 3 Watt, 1% Tol




TE Part #747238-4  
25 MSFL PLUG RA 318 (IN,FM)



TE Part #2212243-1  
FORGE, ASSY PIN, 0#0-4#4-0#8-0#12-0#22



TE Part #1393366-1  
V23540X7000Y 21=GET-FEM TERM S



TE Part #1-1986712-2  
SCREWLESS, SW,12P,5.08 PCB

Documents

Product Drawings  
FORGE, ASSY SCKT, 0#0-4#4-0#8-0#12-0#22  
English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_2212245-1\_2.2d\_dxf.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2212245-1\_2.3d\_igs.zip  
English  
Customer View Model  
ENG\_CVM\_CVM\_2212245-1\_2.3d\_stp.zip  
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



1-1773875-1\_FORGE\_DRAWER\_CONNECTORS\_CN

3-1773463-3\_FORGE\_DRAWER\_CONNECTORS

English

Product Specifications

Application Specification

English

Application Specification

English