


FASTON 250

TE Internal #: 1969507-3

TE Internal Description: 250 FASTON HSG.,FLAG,REC.,1 POS,
BLACK

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | **FASTON 250**







Compression Connectors(4)




Crimp Terminal Housings(142)




Insertion & Extraction Tools(6)




Magnet Wire Terminals(1)



PCB Terminals(135)




Quick Disconnects(445)




Splices(4)


Customers Also Bought




TE Part #1971777-5
PTL TPA HIGH TEMP 1 x 5 BLACK




TE Part #2-1744036-6
06P ECONOMY POWER .200 CL HSG




TE Part #1742883-1
187 FASTON,REC.,20-16 AWG,NPST




TE Part #1742543-1
250 FASTON,FLAG,REC.,18-12 AWG, NPST




TE Part #3-963217-1
16 J-P-T GEH KOMPL




TE Part #5-1971773-7
PTL 1X5 PLUG HSG HIGH TEMP KEY A LGR




TE Part #W6P-P004
WEDGE LOCK



TE Part #1-1969443-0
EP 2.5 TPA Retainer, 10 Pos



TE Part #521766-1
250 HSG. PL MKIII REC. 10mm 2P NAT



TE Part #1534072-3
MULTIF.ASSY MK2 3POS,AR

Documents



Product Drawings

250 FASTON HSG.,FLAG,REC.,1 POS,BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969507-3_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969507-3_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969507-3_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English