




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Header**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board**

Number of Positions: **9**

Centerline (Pitch): **3.96 mm [.155 in]**

Features

Product Type Features

Header Type	Partially Shrouded
Rectangular Power Connector Type	Header
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Columns	9
Number of Loaded Positions	9
Number of Positions	9
PCB Mount Orientation	Right Angle
Number of Power Positions	9
Number of Rows	1

Electrical Characteristics



Operating Voltage	250 VDC
-------------------	---------

Contact Features

Contact Mating Area Plating Material	Tin
Contact Base Material	Brass
Contact Current Rating (Max)	8 A
Contact Retention Within Housing	Without
Contact Type	Pin
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.032 µm[80 µin]

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	3.96 mm[.155 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

Connector Height	8.21 mm[.323 in]
Product Width	9.4 mm[.37 in]
Product Length	35.64 mm[1.4 in]

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
Circuit Application	Power

Industry Standards

UL Rating	Recognized
Agency/Standard	UL
UL Flammability Rating	UL 94V-0



Glow Wire Rating	Glow Wire
------------------	-----------

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2132781-9
09P EP-II HOUSING, NATURAL

TE Part # 1744416-9
9 POS EP II HSG, GLOW WIRE

TE Part # 1744036-9
09P ECONOMY POWER .200 CL HSG

TE Part # 1744109-4
3.96 EP Hdr Assy, 9P, Omitted #8, Blue



TE Part # 1744525-5
EP RA 05P HEADER ASY NO 3 PIN

TE Part # 1744544-9
EP II TPA 09P, BLACK

TE Part # 3-1744525-9
3.96 EP HDR ASSY 9P R/A, NO 6,8 PINS

Also in the Series | Economy Power

Connector Contacts(1)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(162)

PCB Latches, Locks & Retainers(2)

Power Contacts(8)

Rectangular Connector Housings(1)

Rectangular Power Connectors(302)

Wire-to-Board Connector Assemblies & Housings(142)

Wire-to-Board Connector Contacts(6)

Customers Also Bought

TE Part #5787362-9
100 50SR R/A RCP ASSY,RDSN L/F

TE Part #5788800-2
25 HTMSFL ASSY RA 318 (IN,BL)

TE Part #1-1123723-4
3.96 EP HDR ASSY 4P(NATURAL)

TE Part #63951-1
250 FASTON TAB TPBR



TE Part #284392-2
TERMI-BLOK PCB SIDE ENTRY STAC

TE Part #284392-3
TERMI-BLOK PCB SIDE ENTRY STAC

TE Part #796644-4
4POS 5.0MM CE R/A HDR,TRM BLK

TE Part #5-2301996-5
RJ45 JACK INT.MAG. 10/100 LED 1X2 INV.

TE Part #1-2176340-1
CRGCQ 0603 47R 5%

TE Part #1744489-9
3.96 EP HDR ASY 09P NO PEG, GW

Documents

Product Drawings

3.96 EP HDR ASSY 9P R/A, GW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1744428-9_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1744428-9_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1744428-9_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Economy Power II (EP II) Glow Wire test compliant connectors

English

1-1773885-9 Economy Power Connectors

English

Product Specifications

Application Specification

Japanese



Application Specification

English

Agency Approvals

UL Report

English