

ATGBICS JL275A-C network transceiver module Fiber optic 100000 Mbit/s QSFP 1310 nm

Brand : ATGBICS

Product code: JL275A-C

Product name : JL275A-C



HPE Compatible Transceiver QSFP28 100GBase-LR4 1310nm SMF 10km LC DOM


ATGBICS JL275A-C network transceiver module Fiber optic 100000 Mbit/s QSFP 1310 nm:

ATGBICS JL275A 100GBase-LR4 QSFP28 supports a distance of up to 10km over single-mode fibre (SMF) using a wavelength of 1310nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product is built to the exact specification of HPE JL275A= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.



ATGBICS JL275A-C. SFP transceiver type: Fiber optic, Maximum data transfer rate: 100000 Mbit/s, Interface type: QSFP. Product colour: Silver, Housing material: Metal, Country of origin: China. Input voltage: 3.3 V, Maximum voltage: 3.5 V, Power consumption (typical): 4 W. Width: 13.5 mm, Depth: 72.4 mm, Height: 18.4 mm. Number of products included: 1 pc(s), Package type: Box

Performance		Features	
SFP transceiver type *	Fiber optic	Brand compatibility	HP
Maximum data transfer rate *	100000 Mbit/s	Power	
Interface type *	QSFP		
Single-mode fiber (SMF) supported	✓		Input voltage
Multi-mode fiber (MMF) supported	✗		Maximum voltage
Fiber optic connector	LC		Power consumption (typical)
SFP transceiver standard	LR4	Operational conditions	
Maximum transfer distance	10000 m		Maximum operating temperature
Wavelength	1310 nm		Operating temperature (T-T)
Ethernet LAN	✓		Storage temperature (T-T)
Ethernet interface type	100 Gigabit Ethernet		Operating relative humidity (H-H)
Digital Diagnostics Monitoring (DDM)	✓		Storage relative humidity (H-H)
Features		Weight & dimensions	
Product colour	Silver	Width	13.5 mm
Housing material	Metal	Depth	72.4 mm
Plug and Play	✓	Height	18.4 mm
Hot-Plug support	✓	Weight	42 g
Hot-swap	✓	Packaging data	
Easy to install	✓		Number of products included
Country of origin	China		1 pc(s)
			Package type
			Box
Technical details			
		Sustainability certificates	RoHS



5056468759719

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.